

Disposable Filter Units | #9933-05-BQ

Parker Balston disposable filter units offer all the advantages of microfibre filter cartridges for high efficiency liquid and gas filtration combined with the economics and convenience of complete disposability.

Technical Specifications

Maximum Operating Temperature (F):	230	Filtration Efficiency:	99.99%
Materials of Construction:	Nylon	Maximum Flow Rate (cfm):	5.3
Port Connection (inch):	1/4	Port Connection Type:	Tube
Height (inch):	3.2	Maximum Operating Pressure:	125 psig, 8.62 barg
Filter Type:	In-Line	Maximum Flow Rate:	9.1 m3/min, 5.4 CFM
Micron Rating:	0.01 µm	Maximum Operating Temperature:	230 °F, 110 °C
Minimum Operating Temperature:	-40 °F, -40 °C	Width:	1 inch, 25.4 mm
Height:	83.2 mm, 3.2 inch	Weight:	0.7 oz, 19.8 g
Drain Port Size:	N.A.	Compatible Element:	N.A.
Brand:	Balston	Port Size:	1/4 inch
Materials of Construction:	Nylon	Port Type:	Tube