



Sliver for SFF-TA-1002

TE Internal #: 2327679-5

Sliver for SFF-TA-1002, PCB Edge Card, Vertical, Cable-to-Board,
56 Position, Surface Mount, Sliver for SFF-TA-1002, Internal I/O
Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Internal I/O Connectors



Internal I/O Connector Type: **Sliver for SFF-TA-1002**

Connector Mates With: **PCB Edge Card**

PCB Mount Orientation: **Vertical**

Connector System: **Cable-to-Board**

Number of Positions: **56**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Internal I/O Connector Type	Sliver for SFF-TA-1002
Connector Mates With	PCB Edge Card
Connector System	Cable-to-Board

Configuration Features

Number of Rows	2
PCB Mount Orientation	Vertical
Number of Positions	56

Contact Features

PCB Contact Termination Area Plating Material	Tin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	1.1 A



Contact Mating Area Plating Material Thickness	.381 μm[15 μin]
--	-----------------

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	.6 mm[.023 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Industry Standard	EDSFF, Gen-Z
-------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2360871-3
56 POSITION SLIVER ORTHOGONAL
EDSFF 1*1




TE Part # 2327677-1
RECEPT ASSY, 140 POS, VERT, SLIVER
2.0




TE Part # 2328461-1
280 POS., CONNECTOR ASSEMBLY,
SLIVER 2.0



TE Part # 2333799-1
RCPT ASSY, VERT, 168 POS, SLIVER 2.0



TE Part # 2360871-1
56 POSITION SLIVER ORTHOGONAL
EDSFF 1*1




TE Part # 2360871-2
56 POSITION SLIVER ORTHOGONAL
EDSFF 1*1

Also in the Series | Sliver for SFF-TA-1002



Connector Hardware(1)



Internal I/O Cable Assemblies(105)



Internal I/O Connectors(133)

Customers Also Bought



TE Part #1-6600383-9
MBXL VERT HDR 1P+24S+1P STR



TE Part #2302407-1
QSFP+ ASSY, 2X1, GSKT, 2LP-OUTR,
W/ CS GA



TE Part #2007882-3
IMP100S,H,V6P10C,UG,DEW46,5.5



TE Part #2335232-1
ASSY, SMT BATTERY CONN





TE Part #2185223-1
ASSY, SEATING TOOL, QSFP



TE Part #2132464-1
IMP100O,R,RA4P8C,LG,39



TE Part #3-2180324-2
zSFP+ STACKED 2X4 RECEPTACLE ASSEMBLY



TE Part #1888566-2
IMJ,1X1,PNL GRD,LED(Y/G), SN



TE Part #2057415-1
IMP100S,R,RA4P8C,LG,39

TE Part #2226412-1
ASSY PIN MODULE, 16-02 PCB RA, STD

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2327679-5_11.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2327679-5_11.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2327679-5_11.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Sliver Internal Cabled Interconnect Solutions Brochure (Chinese)

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English