

24-0020

Class 0 14" / 36cm Red



| | |
|-----------|--|
| Category | A/C |
| Class | 0 |
| Cuff | Straight with beaded edge |
| Max Use | 1000V |
| Type | 1 |
| Colour | Red |
| Length | 14" / 36cm |
| Sizes | 8-11 |
| Packaging | 1 pair p/polybag and individual box. 10 pairs p/carton |

Features & Benefits

- Made from 100% natural high grade rubber latex
- Smooth chlorinated surface finish and rolled cuff edge aid donning and doffing
- Environmentally friendly dipping process free from the use of solvents
- Ergonomic design and finger shape minimises hand fatigue
- Increased flexibility in cold environments
- Silicone-free
- Double certification EN 60903 and ASTM D120



Applications / Industries

- Power Utilities and Public Works
- Electric Public Transport Maintenance
- EV Battery Manufacturing and assembly
- EV Aftermarket Service and Maintenance
- Electrical Maintenance
- Excavation and Cable Laying
- Cable Jointing
- Field Services



Performance



Manufactured and tested in accordance with IEC 60903, EN 60903 and ASTM D120.



Special Categories Classes

Meets the special properties:

A-Acid C-Extreme low temperature
H-Oil resistant Z-Ozone
R = A + Z + H

| CLASS | LENGTH CM/INCH | CATEGORIES | PROOF TEST VOLTAGE AC/DC | MAXIMUM USE VOLTAGE AC/DC | SIZES |
|----------------|----------------|------------|--------------------------|---------------------------|---------------|
| Class 00 Beige | 28/11 36/14 | A/C | 2.500/10.000 | 500/750 | 8, 9, 10, 11 |
| Class 0 Red | 28/11 36/14 | A/C | 5.000/20.000 | 1.000/1.500 | 8, 9, 10, 11 |
| Class 1 White | 36/14 | A/C | 10.000/40.000 | 7.500/11.250 | 8, 9, 10, 11 |
| Class 2 Yellow | 36/14 | A/C/H | 20.000/50.000 | 17.000/25.500 | 8, 9, 10, 11 |
| Class 3 Green | 36/14 | A/C/H | 30.000/60.000 | 26.500/39.750 | 8, 9, 10, 11 |
| Class 4 Orange | 41/16 | A/C/H | 40.000/70.000 | 36.000/54.000 | 9, 10, 11, 12 |

Product Packaging

Each pair is supplied in an air sealed polybag and individual box.

Outer cartons contain 10 pairs of individual pair boxes.

