

M18 FDGROVB / M18 FDGROVPDB | M18 FUEL™ VARIABLE SPEED BRAKING DIE GRINDER



- Up to (35) pipes deburred per M18 5.0Ah battery charge
- 5 variable speed settings to match speed to application, ranging from 8,000 to 20,000 RPM, providing increased control
- RAPIDSTOP™ Brake stops accessory in less than 2 seconds, enhancing safety
- Spindle lock allows for one wrench accessory change
- Maximum accessory compatibility with 55mm cutting wheel and 76mm sanding wheel
- LED Light illuminates grinding zone

*Slide and Paddle Switch versions available.
Version availability subject to region

Battery System	M18
Variable Speed (RPM)	8,000 / 11,000 / 14,000 / 17,000 / 20,000
Max. Accessory Capacity	76mm Sanding Wheel 55mm Cutting Wheel
Collet Size	6mm / 8mm
Braking	Yes
Spindle Lock	Yes
LED Light	Yes
Tool Length	410mm
Weight (w/ 5.0Ah Battery)	2.13 KG
Recommended Battery	M18 5.0Ah