

FGW40N120VD

Discrete IGBT


Discrete IGBT (High-Speed V series) 1200V / 40A

■ Features

Low power loss Low switching surge and noise High reliability, high ruggedness (RBSOA, SCSOA etc.)

Applications

Inverter for Motor drive AC and DC Servo drive amplifier Uninterruptible power supply




Equivalent circuit

Collector

■ Maximum Ratings and Characteristics

● Absolute Maximum Ratings (at T_c=25°C unless otherwise specified)

Items	Symbols	Characteristics	Units	Remarks
Collector-Emitter voltage	Vces	1200	V	
Gate-Emitter voltage	V _{GES}	±20	V	
DC Collector Current	Ic@25	63	Α	Tc=25°C, Tj=150°C
	Ic@100	40	Α	Tc=100°C, Tj=150°C
Pulsed Collector Current	I _{CP}	80	Α	Note *1
Turn-Off Safe Operating Area	-	80	Α	Vce≤1200V, Tj≤175°C
Diode Forward Current	I _{F@25}	58	Α	
	IF@100	30	Α	
Diode Pulsed Current	IFP	80	Α	Note *1
Short Circuit Withstand Time	tsc	10	μs	Vcc≤640V, V _{GE} =15V T _J ≤150°C
IGBT Max. Power Dissipation	P _{D_IGBT}	340	W	Tc=25°C
FWD Max. Power Dissipation	P _{D_FWD}	220	۷V	Tc=25°C
Operating Junction Temperature	T _j	-40~+175	°C	
Storage Temperature	T _{stg}	-55~+175	°C	



Note *1 : Pulse width limited by Tjmax.

● Electrical characteristics (at T_j= 25°C unless otherwise specified)

Itama	Symbols	Symbols Conditions		Characteristics				
Items	Symbols	Conditions	min.	typ.	max.	Unit		
Collector-Emitter Breakdown Voltage	V _{(BR)CES}	$I_{C} = 50 \mu A, V_{GE} = 0 V$	1200	-	-	V		
Zero Gate Voltage Collector Current	Ices	V _{CE} = 1200V, V _{GE} = 0V	-	-	250	μA		
		/ Ij=1/5°C	-	-	2	mA		
Gate-Emitter Leakage Current	Iges	$V_{CE} = 0V$, $V_{GE} = \pm 20V$	-	-	200	nA		
Gate-Emitter Threshold Voltage	V _{GE (th)}	V _{CE} = +20V, I _C = 40mA	6.0	6.5	7.0	V		
Collector-Emitter Saturation Voltage	V _{CE} (sat)	V _{GE} = +15V. I _C = 40A	-	1.85	2.4	V		
		I _j =1/5°C	-	2.4	-	•		
Input Capacitance	Cies	V _{CE} =25V	-	2230	-	_		
Output Capacitance	Coes	V _{GE} =0V	-	135	-	pF		
Reverse Transfer Capacitance	Cres	f=1MHz	-	105	-			
0-4- Oh		Vcc = 600V			-	0		
Gate Charge	Q _G	Ic = 40A	-	320		nC		
Turn-On Delay Time	4	V _{GE} = 15V T _i = 25°C		38				
Rise Time	t _{d(on)}	V _{cc} = 600V	-	75	-			
Turn-Off Delay Time	t _{d(off)}	I _c = 40A	-	310	-	ns		
Fall Time	t _f	V _{GF} = 15V	-	55	-	-		
Turn-On Energy	Eon	$R_{\rm G} = 10\Omega$	- 55					
Turn-On Linergy	Lon	L = 500µH	_	4.5	-	mJ		
Turn-Off Energy	Eoff	Energy loss include "tail" and FWD reverse	_	2.2	-			
		recovery.						
Turn-On Delay Time	t _{d(on)}	T ₁ = 175°C	<u> </u>	38	-			
Rise Time	t	V _{cc} = 600V	-	68	-	ns		
Turn-Off Delay Time	t _{d(off)}	Ic = 40A	-	360	-			
Fall Time	tr	V _{GE} = 15V	-	85	-			
Turn-On Energy	Eon	$R_G = 10\Omega$	-	6.5	-			
•		L = 500µH			-	mJ		
Turn-Off Energy	Eoff	Energy loss include "tail" and FWD reverse	-	3.8				
		recovery.						
Forward Voltage Drop V _F	Ve	I _F =30A T _j =25°C	-	1.7	2.21	V		
	V F	I _j =1/5°C	-	1.8	-	V		
		Vcc=30V						
Diode Reverse Recovery Time trr1	t _{rr1}	I _F = 3.0A	-	79	103	ns		
D. 1 D. T.		-di/dt=200A/μs						
Diode Reverse Recovery Time	t _{rr2}	Vcc=600V	_	0.33	-	μs		
		I⊧=30A	-		-			
Diode Reverse Recovery Charge	Qrr	-di⊧/dt=200A/μs	-	1.45	-	μC		
, ,		T _j =25°C						

FGW40N120VD

http://www.fujielectric.com/products/semiconductor/


Itama	Cumbala	Conditions	Characteristics			Unit
Items Symbols	Symbols		min.	typ.	max.	Unit
Diode Reverse Recovery Time	t _{rr2}	Vc=600V I⊧=30A	-	0.75	-	μs
Diode Reverse Recovery Charge	Qrr	-di⊧/dt=200A/μs T.=175°C	-	4.30	-	μC

● Thermal resistance


Items	Symbols		Unit		
items	Symbols	min.	typ.	max.	Oilit
Thermal Resistance, Junction-Ambient	R _{th(j-a)}	-	-	50	
Thermal Resistance, IGBT Junction to Case	R _{th(j-c)_IGBT}	-	-	0.439	°C/W
Thermal Resistance, FWD Junction to Case	R _{th(j-c)_FWD}		-	0.676	

■ Characteristics (Representative)


Graph.1 DC Collector Current vs T_c $V_{ce} \ge +15V$, $T_i \le 175$ °C




Graph.3 Typical Output Characteristics ($V_{\text{ce-}}I_{\text{c}}$) T_{j} =25°C




Graph.5 Typical Transfer Characteristics V_{ce} =+15V




Graph.2 Collector Current vs. switching frequency V_{og} =+15V, T_{o} ≤175°C, V_{co} =600V, D=0.5, R_{o} =10 Ω , T_{o} =100°C




Graph.4 Typical Output Characteristics (V_{CE} - I_C) T_i =175°C




Graph.6
Gate Threshold Voltage vs. T_i
I_c=40mA, V_{cr}=20V




Graph.7 Typical Capacitance V_{□E}=0V, f=1MHz, T_i=25°C




Graph.9 Typical switching time vs. Io T_i=175°C, V_{∞}=600V, L=500 μ H V_{ω}=15V,R $_{\omega}$ =10 Ω




Graph.11 Typical switching losses vs. I_c T_j=175°C, V_{cc} =600V, L=500 μ H V_{ce} =15V, R_e =10 Ω




Graph.8 Typical Gate Charge V∞=600V, I₀=40A, T₀=25°C




Graph.10 Typical switching time vs. $R_{\rm s}$ T₁=175°C, $V_{\rm cc}$ =600V, $I_{\rm c}$ =40A, L=500 μ H $V_{\rm sc}$ =15V




Graph.12 Typical switching losses vs. R_{G} T_J=175°C, V_{cc}=600V, I_c=40A, L=500 μ H V_{GE}=15V




Graph.13 FWD Forward voltage drop (V_F-I_F)




Graph.15 Typical reverse recovery loss vs. I_F $T_{\rm J}=175^{\circ}C,V_{\rm cc}=600V,L=500\mu H$ $V_{\rm cE}=15V,R_{\rm c}=10\Omega$




Graph.14 Typical reverse recovery characteristics vs. I_F T_j =175°C, V_{∞} =600V, L=500 μ H,




Graph.16 Reverse biased Safe Operating Area $T_i \le 175^{\circ}C$, $V_{\text{ce}} = +15 \text{V}/0 \text{V}$, $R_{\text{c}} = 10 \Omega$




Graph.17
Transient thermal resistance of IGBT



Graph.18
Transient thermal resistance of FWD



■ Outline Drawings, mm



WARNING

- 1. This Catalog contains the product specifications, characteristics, data, materials, and structures as of May 2011.

 The contents are subject to change without notice for specification changes or other reasons. When using a product listed in this Catalog, be sur to obtain the latest specifications.
- 2. All applications described in this Catalog exemplify the use of Fuji's products for your reference only. No right or license, either express or implied, under any patent, copyright, trade secret or other intellectual property right owned by Fuji Electric Co., Ltd. is (or shall be deemed) granted. Fuji Electric Co., Ltd. makes no representation or warranty, whether express or implied, relating to the infringement or alleged infringement of other's intellectual property rights which may arise from the use of the applications described herein.
- 3. Although Fuji Electric Co., Ltd. is enhancing product quality and reliability, a small percentage of semiconductor products may become faulty. When using Fuji Electric semiconductor products in your equipment, you are requested to take adequate safety measures to prevent the equipment from causing a physical injury, fire, or other problem if any of the products become faulty. It is recommended to make your design failsafe, flame retardant, and free of malfunction.
- 4. The products introduced in this Catalog are intended for use in the following electronic and electrical equipment which has normal reliability requirements.
- Computers
- OA equipment
- Communications equipment (terminal devices)
- Measurement equipment

- Machine tools
- Audiovisual equipment
- Electrical home appliances Personal equ
- 5. If you need to use a product in this Catalog for equipment requiring higher reliability than normal, such as for the equipment listed below, it is imperative to contact Fuji Electric Co., Ltd. to obtain prior approval. When using these products for such equipment, take adequate measures such as a backup system to prevent the equipment from malfunctioning even if a Fuji's product incorporated in the equipment becomes faulty.
- Transportation equipment (mounted on cars and ships)
- Trunk communications equipment

• Traffic-signal control equipment

- Gas leakage detectors with an auto-shut-off feature
- Emergency equipment for responding to disasters and anti-burglary devices
 Medical equipment
- Safety devices
- 6. Do not use products in this Catalog for the equipment requiring strict reliability such as the following and equivalents to strategic equipment (without limitation).
 - · Space equipment

- Aeronautic equipment
- Nuclear control equipment

- Submarine repeater equipment
- 7. Copyright ©1996-2011 by Fuji Electric Co., Ltd. All rights reserved.

 No part of this Catalog may be reproduced in any form or by any means without the express permission of Fuji Electric Co., Ltd.
- 8. If you have any question about any portion in this Catalog, ask Fuji Electric Co., Ltd. or its sales agents before using the product.

 Neither Fuji Electric Co., Ltd. nor its agents shall be liable for any injury caused by any use of the products not in accordance with instructions set forth herein.