# TEF4-ON

#### General Information

Extended Product Type: TEF4-ON

Product ID: 1SBN020112R1000

EAN: 3471523130630

Catalog Description: TEF4-ON Frontal Electronic Timer

Long Description: TEF4-ON Frontal Electronic Timer

# Categories

Products » Low Voltage Products and Systems » Control Products »
Contactors » Block Contactors Accessories

### Ordering

**EAN:** 3471523130630 **Minimum Order Quantity:** 1 piece **Customs Tariff Number:** 85389091

#### Dimensions

Product Net Weight: 0.065 kg

# Container Information

Package Level 1 Units: 1 piece Package Level 1 Width: 82 mm Package Level 1 Height: 51 mm Package Level 1 Length: 56 mm Package Level 1 Gross Weight: 0.06500 kg Package Level 1 EAN: 3471523130630 Package Level 2 Units: 80 piece Package Level 2 Width: 254 mm Package Level 2 Height: 200 mm Package Level 2 Length: 319 mm Package Level 2 Gross Weight: 6.800 kg Product Packing Type: Box Packing Type: Box

#### Environmental

Ambient Air Temperature:

Close to Contactor for Storage -40...+80 °C
Near Contactor for Operation in Free Air -25...+70 °C

Maximum Operating Altitude
Permissible:

Resistance to Vibrations acc. to IEC 5 ... 300 Hz 3 g Closed position / 2 g Open position 60068-2-6:

# Technical UL/CSA

Tightening Torque UL/CSA: Auxiliary Circuit 11 in-lb

#### Additional Information

Conventional Free-air Thermal acc. to IEC 60947-5-1, q=40°C 5 A

Current (I<sub>th</sub>):

Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20

**IIT Publishing Status:** Level 0 - Information enabled Maximum Electrical Switching AC-15 1200 cycles per hour DC-13 900 cycles per hour Frequency:

Maximum Mechanical Switching

Frequency:

3600 cycles per hour

Mounting Position: Mounting positions 1, 1 +/- 30°, 2, 3, 4, 5

Number of Auxiliary Contacts NC: Number of Auxiliary Contacts NO: 1

**Product Main Type:** Accessories for Block Contactors

**Product Name:** Electronic Timer

Rated Frequency (f): Auxiliary Circuit 50 / 60 Hz

Rated Impulse Withstand Voltage

Rated Insulation Voltage (Ui):

acc. to UL/CSA 300 V

acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 400 V

Rated Operational Current AC-15 (220 / 240V) 1.5 A

(24 / 127V) 3 A Rated Operational Current DC-13 (24V) 1 A / 24 W

(l¸):

Rated Short-time Withstand Current for 0.1s 8 A for 1.0s 8 A (I<sub>cw</sub>): Screw Terminals **Terminal Type:** Timer Relay Type: ON-delay

# Certificates and Declarations (Document Number)

**CB Certificate:** CB CN 24746 Declaration of Conformity - CE: 1SBD250171C1000

# Classifications

ETIM 4.0:	EC002498 - Accessories for low-voltage switch technology
ETIM 5.0:	EC002498 - Accessories for low-voltage switch technology
Object Classification Code:	K