




Part Number : [5051521400](#)

Product Description : DuraClik Wire-to-Board 2-Way Terminal Position Assurance (TPA) Retainer, 14 Circuits

Series Number : 505152

Status : Active

Product Category : Connector Accessories



Documents & Resources

Drawings

[5051521400_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-505151-002-001.pdf](#)

[AS-505151-001-001.pdf](#)


[SPK-505152-001-001.pdf](#)

[5051510002-000.pdf \(Gold Plating\)](#)

[PS-505151-001-001.pdf \(Tin Plating\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	505152
Description	DuraClik Wire-to-Board 2-Way Terminal Position Assurance (TPA) Retainer, 14 Circuits
Application	Automotive
Component Type	Terminal Position Assurance
Product Name	DuraClik
UPC	887191735269

Electrical

Current - Maximum per Contact	3.0A
-------------------------------	------

Physical

Circuits (Loaded)	14
Circuits (maximum)	14
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	165.100/mg

Number of Rows	1
Packaging Type	Bag
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Crimp or Compression

Mates With / Use With

Use with Part(s)

Description	Part Number
DuraClik TPA Single Row Receptacle Housings	<u>505151</u>
DuraClik TPA Female Crimp Terminals	<u>505153</u>