

FAG



X-life

22315-E1-XL-K

Spherical Roller Bearing

Spherical roller bearings 223...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information



Your current product variant

Design	E1	without central rip
Bore type	K	Tapered, taper 1:12
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication feature	Standard	

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width
C _r	445,000 N	Basic dynamic load rating, radial
C _{0r}	450,000 N	Basic static load rating, radial
C _{ur}	42,000 N	Fatigue load limit, radial
n _G	4,500 1/min	Limiting speed
n _{gr}	3,550 1/min	Reference speed
≈m	5.174 kg	Weight



Mounting dimensions

d _{a min}	87 mm	Minimum diameter shaft shoulder
d _{a max}	92 mm	Maximum diameter of shaft shoulder
D _{a max}	148 mm	Maximum diameter of housing shoulder
r _{a max}	2.1 mm	Maximum recess radius
d _{b min}	82 mm	Minimum cavity diameter of the sleeve
B _{a min}	5 mm	Minimum cavity width of the sleeve

Dimensions

r _{min}	2.1 mm	Minimum chamfer dimension
D ₁	136.3 mm	Bore diameter outer ring
d ₂	92.4 mm	Raceway diameter of the inner ring
d _s	4.8 mm	Diameter lubrication hole
n _s	9.5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0.34	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	1.99	Dynamic axial load factor
Y ₂	2.96	Dynamic axial load factor
Y ₀	1.94	Static axial load factor

Additional information

H2315	Adapter sleeve
AHX2315G	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment