

iEM3115 energy meter - 63 A - 2 digital I - multi-tariff - MID

Local distributor code:

397406689 A9MEM3115

EAN Code: 3606480481505

Main

Range	Acti9
range of product	Acti9 iEM3000
Product or component type	Energy meter
Device short name	iEM3115
Market segment	Buildings small building cost management: billing: main incomer Buildings small building cost management: billing: sub feeder Buildings medium building cost management: billing: panelboard Buildings medium building cost management: billing: sub feeder Buildings medium building cost management: billing: sub feeder Buildings medium building cost management: billing: panelboard Buildings large building cost management: billing: main incomer Buildings large building cost management: billing: main incomer Buildings large building cost management: billing: sub feeder Buildings multi-site cost management: billing: panelboard Buildings multi-site cost management: billing: sub feeder Buildings multi-site cost management: billing: panelboard Data center cost management: billing Healthcare cost management: billing Industry cost management: billing Buildings small building cost management: cost allocation: main incomer Buildings small building cost management: cost allocation: sub feeder Buildings medium building cost management: cost allocation: panelboard Buildings medium building cost management: cost allocation: sub feeder Buildings medium building cost management: cost allocation: main incomer Buildings medium building cost management: cost allocation: panelboard Buildings large building cost management: cost allocation: sub feeder Buildings large building cost management: cost allocation: main incomer Buildings large building cost management: cost allocation: sub feeder Buildings multi-site cost management: cost allocation: main incomer Buildings multi-site cost management: cost allocation: sub feeder Buildings multi-site cost management: cost allocation: panelboard Data center cost management: cost allocation Industry cost management: cost allocation

Complementary

Poles description	1P + N	
•	3P + N	
	3P	
Type of measurement	Active energy	
Device application	Sub billing	
	Multi-tariff	
Accuracy class	Class 1 active energy conforming to IEC 62053-21	
	Class 1 active energy conforming to IEC 61557-12	
	Class B active energy conforming to EN 50470-3	
input type	Direct connection	
[In] rated current	63 A	

	100277 V 173480 V	
Network frequency	60 Hz 50 Hz	
Technology type	Electronic	
Display type	LCD display	
Sampling rate	32 samples/cycle	
Measurement current	063 A	
Maximum value measured	9999999.9 kWh	
tariff input	Tariff (4)	
Communication port protocol	-	
Communication port support	-	
Local signalling	Green indicator light: power ON Yellow flashing LED: accuracy checking	
Number of inputs	2 digital 05 V/1140 V 24 V DC	
Number of outputs	0	
Mounting mode	Clip-on	
Mounting support	DIN rail	
Connections - terminals	Screw terminals 16 mm² cable(s)	
Overvoltage category	III	
Standards	BS EN 61557-12:2021 IEC 61557-12:2021 EN 61557-12:2021 BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 62052-11:2020	

Product certifications	CF		
Product certifications	CE conforming to IEC 61010-1 (safety)		
	CE conforming to EN 61557-12 (power monitor)		
	CE conforming to EN/IEC 61326-1 (EMC)		
	UKCA conforming to BS EN 61010-1 (safety)		
	UKCA conforming to BS EN 61557-12 (power monitor)		
	UKCA conforming to BS EN 61326-1 (EMC)		
	CULus conforming to UL 61010-1 (safety)		
	CULus conforming to EN 61010-1 (safety)		
	EAC conforming to EN 50470-3 (sub-meter)		
	RCM conforming to EN 62052 (sub-meter)		
	KZ conforming to EN 50470-3 (sub-meter)		
	METAS conforming to EN 50470-1 (sub-meter)		
	MID conforming to EN 50470-3 (sub-meter)		
	MID conforming to EN 50470-1 (sub-meter)		
	NMI conforming to NMI M 6-1		
Market segment	Residential		
•	Small commercial		
Compatibility code	IEM3115		

Environment

IP degree of protection	IP40 front panel: conforming to IEC 60529 IP20 body: conforming to IEC 60529	
Pollution degree	2	
Relative humidity	595 % at 50 °C	
Ambient air temperature for operation	-2555 °C - MID -2570 °C - IEC	
Ambient air temperature for storage	-4085 °C	
Operating altitude	< 3000 m	
Colour	White	
9 mm pitches	10	
Width	90 mm	
Height	95 mm	
Depth	69 mm	

Packing Units

r adming dimes	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.700 cm
Package 1 Width	9.400 cm
Package 1 Length	10.600 cm
Package 1 Weight	446.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	30
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	14.061 kg
Unit Type of Package 3	P12
Number of Units in Package 3	240

Package 3 Height	45.000 cm	
Package 3 Width	80.000 cm	
Package 3 Length	120.000 cm	
Package 3 Weight	120,960 ka	

Logistical informations

Country of origin CN

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Total lifecycle Carbon footprint	57
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	68ba27e5-f218-482f-94c0-5727d9db28b4
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product datasheet

A9MEM3115

Technical Illustration

User interface / product ON

