



Heat Shrink Tubing > Versafit-V4 Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**

Primary Product Color: **Black**

Shrink Ratio: **2:1**

Wall Type: **Single Wall**

Recovered Inside Diameter (Max): **3.5 mm [.138 in]**

[All Versafit-V4 Heat Shrink Tubing \(16\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Electrical Characteristics

Operating Voltage (Max)	.3 kV
-------------------------	-------

Body Features

Fluid Type	None
Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

Dimensions

Recovered Inside Diameter (Max)	3.5 mm[.138 in]
Expanded Inside Diameter (Min)	7.5 mm[.295 in]
Tubing Size Range	3.5 – 7.1 mm[.138 – .279 in]

Usage Conditions

Shrink Temperature (Min)	70 °C
Tubing Flammability Type	Highly Flame-Retardant



Operating Temperature Range	-30 – 125 °C
Recovery Temperature	90 °C

Operation/Application

Mechanical Resistance	Strain Relief, Wrinkling
-----------------------	--------------------------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Piece
------------------	-------

Other

Meets Low Outgassing Requirements	No
Product Source	China

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM Versafit V4

Dual Wall Tubing(1)

Heat Shrink Tubing(20)

Single Wall Tubing(19)

Customers Also Bought

TE Part #2023374003
ZHTM-5/2.5-0-SP

TE Part #320553
PIDG R 22-16 COMM 22-18 MIL 4

TE Part #EL88842001
VERSAFIT-1/4-0-STK

TE Part #EL88852001
VERSAFIT-1/8-0-STK

TE Part #1757819-6
AMPLIMITE,ASY,PLUG,STD,109,ZN,1,CT

TE Part #CAT-HST-RW175
RW-175 Heat Shrink Tubing

TE Part #CAT-HST-VERSAFITV4
Versafit-V4 Heat Shrink Tubing

TE Part #9422810001
TMS-SCE-3/8-2.0-9

Documents

Product Drawings
V4-7.0-0-SP-SM

English

Datasheets & Catalog Pages



Measuring_Single_Wall_Tubing

English

Selecting_Correct_Tubing_1216

English

Very-Thin-Wall, Highly Flame-Retardant, Metric-Sized Heat-Shrinkable Tubing

English

Versafit v4 Tubing

English

Product Specifications

Application Specification

English