



EN ISO 20345:2011



RESOLUTE TEMPRA 43461-06L

S1P SRC
Size: 36-48
Weight: 620 gr.

Fit: 11

Working Environment:
 Multipurpose, Finishing-off
 building, Logistics and Light
 Industry, ESD Areas


FEATURES

UPPER

 Drummed Suede Leather Hydro
 1,8-2,0 mm
 Reflex insert
 Recycled Digitex Hydro Airy

LINING

3D Green Air 320 gr.

ANTISLIP LINING DUALMICRO

INSOLE

QRS02 Green

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation recycled PS

TYPE

Low Shoe

SOLE

PU / PU ESD-PLUS SRC

 Double density PU sole, Outer- and
 in-between sole with ESD
 compound. For use in contact with
 sensitive electronic equipment.
 Light and comfortable, very
 versatile, highly non-slip SRC
 Antislip standard.

TECHNOLOGIES

Removable Insole


 Anatomical breathable insole.
 Resistant fabric with recycled open-
 cell foam that absorbs shocks and
 reduces fatigue. Eliminates sweat
 with its high ability to evaporate it.
 Continuous comfort for months and
 months of use


Protection elements


 RESISTANT
 TO 3.0 mm.
 NAILS

fibercap sxt

 Composite toecap with fiberglass.
 Resistant to over 200J. Recycled non
 metal perforation resistant insert to
 over 1100 N with a 3.0 mm truncated
 cone nail. Protection over the entire
 sole of the foot. Flexible and
 comfortable


Lateral stability

 dynamic **HC** control
 technology

 Ergonomic rigid internal structure. It
 houses the heel into the right seat,
 adjusting the foot support and control
 of the ankle sideways movements. It
 keeps the foot tight to the shoe,
 allowing the perfect fit.


Torsional stability


STABIL•ACTIVE

 Support made of rigid plastic
 material. It supports the heel bone,
 the instep and tarsal joints, without
 altering energy absorption. A support
 for the natural movement of the foot;
 it provides comfort and greater
 stability.


Electrical features


 ESD footwear discharge static
 electricity and avoid damaging
 surrounding objects; they are
 designed in compliance with the
 following standards: IEC EN
 61340-5-1:2016 - IEC EN
 61340-4-3:2018 - IEC EN
 61340-4-5:2018.

Other


**GREEN
SOLUTION**

 The green proposal by SIXTON
 PEAK®. RESOLUTE GREEN contains
 over 40% of GRS certified recycled
 products with pre and post-consumer
 origins (ratio calculated on the
 surface of the upper)


SRC (SRA+SRB)


 SOLE 43
 PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32	0.39
	HEEL (CONTACT ANGLE 7°) ≥0.28	0.40
SRB STEEL + GLYCEROL	FLAT ≥0.18	0.24
	HEEL (CONTACT ANGLE 7°) ≥0.13	0.23

EN ISO 20344:2011