

FAG



X-life

WS22216-E1-XL-2RSR

Spherical Roller Bearing

Sealed spherical roller bearings WS222...-E1, lip seals on both sides, for continuous casting machines

Technical information



Your current product variant

Design	E1	without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication feature	Standard	
Sealing	2RSR	Seals on both sides, normal temperature
Sealing - excess width	WS	Sealing - excess width

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	140 mm	Outside diameter
B	40 mm	Width
C _r	250,000 N	Basic dynamic load rating, radial
C _{0r}	270,000 N	Basic static load rating, radial
C _{ur}	34,500 N	Fatigue load limit, radial
n _G	1,540 1/min	Limiting speed
≈m	2.435 kg	Weight



Mounting dimensions

d _{a min}	91 mm	Minimum diameter shaft shoulder
D _{a max}	129 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	128.6 mm	Bore diameter outer ring
d ₂	91.3 mm	Raceway diameter of the inner ring
d _s	3.2 mm	Diameter lubrication hole
n _s	6.5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	100 °C	Operating temperature max.

Calculation factors

e	0.22	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	3.14	Dynamic axial load factor
Y ₂	4.67	Dynamic axial load factor
Y ₀	3.07	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Lifetime lubrication, freedom from maintenance
-  Grease Lubrication
-  Sealed on both sides
-  Static angular error and misalignment
-  Dynamic angular error and misalignment