

# D3HC-MP 1.25-2.2L-M-SN-L - Crimp contact



1340372

<https://www.phoenixcontact.com/gb/products/1340372>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, nominal current: 8 A, contact surface: Tin

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1340372       |
| Packing unit                         | 200 pc        |
| Minimum order quantity               | 200 pc        |
| Sales key                            | AABCUA        |
| Product key                          | AABCUA        |
| GTIN                                 | 4063151647056 |
| Weight per piece (including packing) | 0.497 g       |
| Weight per piece (excluding packing) | 0.492 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | CN            |

# D3HC-MP 1.25-2.2L-M-SN-L - Crimp contact



1340372

<https://www.phoenixcontact.com/gb/products/1340372>

## Technical data

### Product properties

|                |               |
|----------------|---------------|
| Product type   | Crimp contact |
| Product family | D3HC-MP-M     |

### Connection data

|                             |           |
|-----------------------------|-----------|
| Stripping length            | 4.5 mm    |
| Conductor cross section AWG | 16 ... 14 |

### Material specifications

|                                          |                    |
|------------------------------------------|--------------------|
| Contact surface                          | Tin Sn             |
| Contact surface material                 | Tin                |
| Metal surface terminal point (top layer) | Tin (1 - 3 µm Sn)  |
| Metal surface contact area (top layer)   | Tin (1 - 3 µm Sn)  |
| Surface characteristics                  | hot-dip tin-plated |
| Contact material                         | Cu alloy           |

### Electrical properties

|                       |     |
|-----------------------|-----|
| Nominal current $I_N$ | 8 A |
|-----------------------|-----|

# D3HC-MP 1.25-2.2L-M-SN-L - Crimp contact



1340372

<https://www.phoenixcontact.com/gb/products/1340372>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460291 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002943 |
|----------|----------|

# D3HC-MP 1.25-2.2L-M-SN-L - Crimp contact



1340372

<https://www.phoenixcontact.com/gb/products/1340372>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)