




Connectors > RF Connectors > Coax Connectors



RF Interface: **F Type**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **8 mm [.315 in]**

Impedance: **75 Ω**

RF Connector Coupling Mechanism: **Push-On**

Features

Product Type Features

RF Interface	F Type
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Body Material	Zinc
Body Plating Material	Tin

Contact Features

--	--



RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Material	Tin (Sn)
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

RF Connector Coupling Mechanism	Push-On
Connector Mounting Type	Board Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Profile Height from PCB	6.83 mm[.269 in]
RF Connector Mated Outer Diameter (Approximate)	8 mm[.315 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	1 GHz
---------------------	-------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Dielectric Material	Polyester, PCT
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.



Solder Process Capability

Pin-in-Paste capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #881545-1

SHUNT LP W/HANDLE 2POS 15AU



TE Part #1-2199298-2

8P,DIP SKT,300 CL,LDR,PB FREE

Documents

Product Drawings

SURFACE MOUNT JACK, F SERIES

English

CAD Files

Customer View Model

ENG_CVM_5415322-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5415322-2_A.3d_stp.zip

English

Customer View Model

ENG_CVM_5415322-2_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

F Series and G Series Connectors



English

Product Specifications

Product Specification

English

Connector, F Series Jack, PCB, Surface Mount

English