



Image may differ from product. See technical specification for details.

BTW 60 CTN9/SP

Super-precision, basic design double direction angular contact thrust ball bearing

These double direction angular contact thrust ball bearings consist of two single row angular contact thrust ball bearings, arranged back-to-back. They accommodate high axial loads in both directions and provide a high degree of system rigidity.

- Accommodate axial loads in both directions
- Maximum system rigidity
- Separable

Overview

Dimensions

Bore diameter	60 mm
Outside diameter	95 mm
Height	44 mm
Contact angle	60 °

Performance

Basic dynamic load rating	30.7 kN
Basic static load rating	83 kN
Attainable speed for grease lubrication	7 500 r/min
Attainable speed for oil-air lubrication	9 000 r/min


Properties

Axial load capability	Double-direction
Number of rows	2
Locating feature, bearing outer ring	None
Design	Basic (BTW series)
Housing washer type (double-row angular contact thrust ball bearings)	Two-piece
Cage	Non-metallic
Tolerance class	SP
Material, bearing	Bearing steel
Coating	Without
Sealing	Without
Lubricant	None
Relubrication feature	Without

Logistics


Product net weight	0.929 kg
eClass code	23-05-10-02
UNSPSC code	31171531

Technical specification



Dimensions

d	60 mm	Bore diameter
D	95 mm	Outside diameter
H	44 mm	Height
d ₁	80.2 mm	Shoulder diameter shaft washer (high shoulder)
D ₁	89 mm	Shoulder diameter housing washer (low shoulder)
2C	22 mm	Height of both housing washers
r _{1,2}	min. 1.1 mm	Shaft washer chamfer radius
r _{3,4}	min. 0.6 mm	Housing washer small chamfer radius



Abutment dimensions

d_a	min. 73 mm	Abutment diameter shaft
D_a	min. 89 mm	Abutment diameter shaft
D_a	max. 90 mm	Abutment diameter housing
r_a	max. 1 mm	Fillet radius
r_b	max. 0.6 mm	Fillet radius

Calculation data

Basic dynamic load rating	C	30.7 kN
Basic static load rating	C_0	83 kN
Fatigue load limit	P_u	4 kN
Attainable speed for grease lubrication		7 500 r/min
Attainable speed for oil-air lubrication		9 000 r/min
Contact angle	α	60 °
Ball diameter	D_w	7.5 mm
Number of rolling element rows	i	2
Number of balls (per bearing)	z	25
Reference grease quantity	G_{ref}	5.2 cm ³

Preload	470 N
Static axial stiffness	618 N/μm

PRELOAD AND STIFFNESS

Axial stiffness for preload A (sets of two brgs back-to-back or face-to-face)	618 N/μm
--	----------

Tolerances and clearances

GENERAL BEARING SPECIFICATIONS

- Tolerances: P4C, SP, UP

PRINCIPLES OF BEARING SELECTION AND APPLICATION

- [Chamfer dimensions](#)
- [Seat tolerances for standard conditions: shafts, housings](#)
- Values for ISO tolerance classes: [shafts](#), [housings](#)
- Speed dependent initial grease fill → [Initial grease fill](#)

More Information

 Product details Designs and variants Markings on bearings General bearing specifications Preload, clearance, and stiffness Loads Attainable speeds Mounting Designation system	 Engineering information Principles of bearing selection and application General bearing knowledge Bearing selection process Bearing failure and how to prevent it	 Tools SimPro Quick SimPro Spindle Bearing Frequency Calculator LubeSelect for SKF greases Heater selection tool
--	---	---



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.