

PFT Slim design female D-coded



Part number	21 03 881 2425
Specification	PFT Slim design female D-coded
HARTING eCatalogue	https://b2b.harting.com/21038812425

Identification

Category	Connector
Series	Circular connectors M12
Identification	M12 Slim Design
Element	Cable connector
Specification	Panel feed through

Version

Termination method	Crimp termination
Gender	Female
Locking type	Screw locking PushPull
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm ²
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	250 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	≥10 ⁸ Ω
Contact resistance	≤10 mΩ
Ambient temperature	-40 ... +85 °C -5 ... +50 °C During connection
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 when mated



Pushing Performance

Technical characteristics

	IP67 when mated
Cable diameter	5.7 ... 8.8 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Isolation group	I ($600 \leq CTI$)

Material properties

Material (insert)	LCP
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
----------	--

Commercial data

Packaging size	10
Net weight	38.7 g
Country of origin	Romania
European customs tariff number	85366990