

M18 FROS125-OB

M18 FUEL™ 125 MM RANDOM ORBIT SANDER

- The M18 FUEL™ sander has a 2.5 mm orbit with 12,000 RPM's which allows a fast and efficient stock removal rate of 220 g of material per charge of one M18™ 5.0 Ah battery
- Fitted with VacLink technology which allows the tool to turn compatible MILWAUKEE® dust extractors on and off via Bluetooth®
- Kitted with our DEK26 vacuum adaptor which will fit directly to all MILWAUKEE® dust extractors. With a dust extraction efficiency of 95%
- Low vibration with levels down to 6.63 ms² allowing the user to sand longer safely
- High performance motor delivers 6,000 to 12,000 sanding strokes per minute with a 2.5 mm orbit and with the ability to choose from five speed settings allows the correct speed to be set for the sanding of different types of materials
- Improved ergonomics and grip for increased user comfort over long periods of sanding with a low weight of only 1.45 kg
- Universal hook and loop sanding pad allows easy changing of sanding discs
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



| | |
|--------------------------------------|---|
| Sanding pad size (mm) | 127 |
| Oscillation diameter (mm) | 2.38 |
| Oscillation rate (opm) | 6,000 - 12,000 |
| No load speed (rpm) | 12,000 |
| Weight with battery pack (EPTA) (kg) | 1.9 (M18 B2) 2.2(M18 B5) 3.0 (M18 B12) |
| Kit included | 2 x M18 B5 Battery packs, M12-18 FC Charger, HD Box |
| Article Number | 4933498254 |

