



Connectors > Connector Accessories > Connector Caps & Covers > Nylon PCB Connector Covers: 2.54mm, MTA 100



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **White**

Primary Product Material: **Nylon**

Number of Positions: **25**

Operating Temperature (Max): **85 °C [185 °F]**

[All Nylon PCB Connector Covers: 2.54mm, MTA 100 \(40\)](#)

Features

Product Type Features

Product Profile	Standard
Connector Cover Type	Strain Relief Cover

Configuration Features

Number of Positions	25
---------------------	----

Body Features

Primary Product Color	White
Primary Product Material	Nylon

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Compatible With IDC Installation Type Connector	Closed End
---	------------



Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 5-641191-5
25P MTA100 CONN ASSY WHT LF



TE Part # 2-640456-5
25P MTA100 HDR ASSY F/L SQ STR



TE Part # CAT-104MTA-NTPMR
Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100



TE Part # CAT-104MTA-NYLCC
Nylon PCB Connector Covers: 2.54 mm, MTA 100



Also in the Series | **MTA 100**

Connector Caps & Covers(69)	Connector Contacts(8)	Connector Hardware(1)	Insertion & Extraction Tools(2)
PCB Headers & Receptacles(441)	Rectangular Connector Housings(1)	Rectangular Power Connectors(1)	Wire-to-Board Headers & Receptacles (441)

Customers Also Bought

TE Part #CAT-AM71-CH8172 AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING	TE Part #281934-2 SINGLE WIRE SEAL	TE Part #114017-ZZ SEALING PLUG, SIZE 12/16, WHT	TE Part #CAT-D48-ST273 DEUTSCH Solid Contacts
TE Part #DT04-2P REC, 2P, GRY, N	TE Part #DT06-2S PLG, 2P, GRY, N	TE Part #CAT-D487-W416 Wedgelocks: DEUTSCH DT	

Documents

Product Drawings
25P MTA100 MOLDED COVER

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_2-643075-5_N.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-643075-5_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-643075-5_N.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_2-643075-5_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_2-643075-5_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_2-643075-5_G.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English