




QSFP56

TE Internal #: 4-2334878-4
QSFP56 to SFP+ Cable Assembly, 16 Positions, 2 m [6.56 ft], 56 Gb/s, Black Cable, Shielded, 26 AWG, .129 mm² Wire, QSFP56 Plug End A, SFP+ Plug End B

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies > QSFP56-Four SFP56 Cable Assembly: 26 AWG



Cable Assembly Type: **QSFP56 to SFP+**
Number of Positions: **16**
Cable Assembly Length: **2 m [6.56 ft]**
Data Rate: **56 Gb/s**
Cable Color: **Black**

[All QSFP56-Four SFP56 Cable Assembly: 26 AWG \(6\)](#)

Features

Product Type Features

Cable Assembly Category	High Speed, Industry Standard
Cable Assembly Type	QSFP56 to SFP+
Cable Style	Madison TurboTwin - Round Jacketed
Cable Assembly (End A)	QSFP56 Plug
Cable Assembly (End B)	SFP+ Plug

Configuration Features

Number of Positions	16
Number of Pairs	8
Number of Signal Positions	16

Electrical Characteristics

Impedance	100 Ω
-----------	-------

Signal Characteristics

--	--



Data Rate	56 Gb/s
-----------	---------

Body Features

Cable Color	Black
Equalized	No
Cable Flammability Rating	CL2

Dimensions

Wire Size	.129 mm²
Outside Cable Diameter	5.96 mm[.235 in]

Operation/Application

Shielded	Yes
Halogen Free	No

Other

Cable Assembly Length	2 m[6.56 ft]
-----------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: MCCP (1.8% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous




materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2316058-1 CAGE ASSEMBLY, 1X4, QSFP28, SPRING, B	 TE Part # 2007262-2 SFP+ 1x2 Cage Assembly, Light SPRING	 TE Part # 2314233-1 QSFP28, 1X3 CAGE ASSEMBLY, SPRING	 TE Part # 2170139-1 SFP+ 1x2 Cage Assembly,W/ Light Pipes
 TE Part # 2007464-5 SFP+ 1x1 Cage Assy, PF,with Heatsink	 TE Part # 2291634-4 SFP+ 1X1 CAGE ASSY, PF,WITH HEATSINK	 TE Part # 2291634-6 SFP+ 1X1 CAGE ASSY, PF,WITH HEATSINK	 TE Part # 2170504-1 SFP+ ,1X6,HEAT SINK,LIGHT,PIPE,EMI Sprin
 TE Part # 2007198-9 SFP+ 1x1 Cage Assembly, Press-	 TE Part # 2294667-5 SFP+ 1X1 CAGE ASSEMBLY, SOLDER TAIL	 TE Part # 2316069-1 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP	 TE Part # 2316805-2 CAGE ASSY, QSFP28 1X1, GASKET, HS
 TE Part # 2297033-4 ZSFP 1X1 CAGE ASSEMBLY PRESSFIT HEATSINK	 TE Part # 2297033-6 ZSFP 1X1 CAGE ASSEMBLY PRESSFIT HEATSINK	 TE Part # 2291634-5 SFP+ 1X1 CAGE ASSY, PF,WITH HEATSINK	 TE Part # 2310520-1 zSFP+ STACKED 2X1 RECEPTACLE ASSEMBLY






TE Part # 2303337-1
SFP+ 1X2 CAGE ASSEMBLY, 2.5MM
SOLDER TYP



TE Part # 2311430-1
SFP+ 1x4 w/ Ultra Low Profile LP



TE Part # 2-2007182-0
SFP Standard 1x2 Light Pipe Assm



TE Part # 2304369-1
SFP+ 1X1 CAGE ASSY, PF,WITH
HEATSINK

Also in the Series |

QSFP56



Pluggable I/O Cable Assemblies(49)

Customers Also Bought



TE Part #3-1879075-1
THS25 39R 5%



TE Part #4-2821224-5
SFP56 DIRECT ATTACH CA, 3M,
26AWG

Documents

Product Drawings

QSFP TO [4]SFP 56GIG 26AWG 2 METER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2334878-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2334878-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2334878-4_A.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English