


DF2210



Electronic circuit breaker

Fuse/IO-Link/24VDC/10A



- 1 panel for labelling
- 2 pushbutton on / off / reset status LED 1
- 3 push-in terminal Output 1



Electrical data

Operating voltage	[V]	to SELV/PELV
Nominal voltage DC	[V]	24
Input voltage DC	[V]	18...30
Protection class		III
Mains buffering time (nominal voltage 24 V DC)	[ms]	10
Closed-circuit current	[mA]	10
Power loss (nominal voltage 24 V DC)	[W]	1.968
Number of channels		1
Nominal current	[A]	10
Nominal current (Fail Safe Element)	[A]	10

Outputs

Load capacitance, total	[mF]	20
-------------------------	------	----

Operating conditions

Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-40...70
Protection		IP 20; (on the front)
Pollution degree		2

Tests / approvals

EMC	EN 61000-6-3	radiation of interference
	EN 61000-6-2	immunity

DF2210




Electronic circuit breaker

Fuse/IO-Link/24VDC/10A

Mechanical data	
Weight [g]	72
Housing	housing for DIN rail mounting
Type of mounting	mounting on DIN rail; (TH35 (EN 60715))
Dimensions [mm]	80 x 12.5 x 98.5


Displays / operating elements		
Display	status	1 x LED, red / green / orange
Operating elements	1 x	pushbutton

Electrical connection	
push-in terminals:	
contact lever/strip:	
Connection	



Diagrams and graphs

output characteristics



time-current characteristics