



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (108-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Manual**

Features

Other

Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (108-)
TE Certification	Yes – Certificate Included
Power Technology Type	Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 3-747579-0
SHLDNG FERRULE, PLTD, BULK PKG


Customers Also Bought




TE Part #CAT-AM7017-H8172
AMP COMMON TERMINATION HOUSINGS




TE Part #3-747579-0
SHLDNG FERRULE, PLTD, BULK PKG




TE Part #66506-9
PIN CONTACT, 20 DF




TE Part #829131P021
ES2000-NO.1-C1-0-STK




TE Part #1658686-2
SOCKET CONT, 22-28 AWG, DF 22, AMPLIMITE



TE Part #34070
PG BUTT SPLC 22-16COMM22-18MIL



TE Part #1658659-1
KIT,HDP-20,ENCLSUR,PLUG,SIZE 3



TE Part #102437-1
MOD IV L.P.



Documents

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

Bottoming Dies

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Instruction Sheets

Crimping Die Assemblies f/AMPLIMITE Connectors

English

Instruction Sheet (U.S.)

English