



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 26
Primary Product Color: Blue
Protection & Strain Relief Accessory Type: Cover Assembly
Primary Product Material: PBT GF
Strain Relief: Without

Features

Product Type Features

Sealable	Yes
Protection & Strain Relief Accessory Type	Cover Assembly

Configuration Features

Number of Positions	26
---------------------	----

Body Features

Primary Product Color	Blue
Primary Product Material	PBT GF

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	100 °C[212 °F]
Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	800

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 185876-2
26W MQS COVER 90 BLUE



TE Part # 144933-1
LEVER FOR MQS



TE Part # CAT-SIGH262
Signal Header



TE Part # 185454-1
26W MQS HDR ASSY FOR SMT

Customers Also Bought



TE Part #2-2298724-9
4P,MATE-AX,PIN HSG ASSY,180DEG, COD Z



TE Part #K1010987
Relay 26-73-04



TE Part #CAT-SIGH262
Signal Header



TE Part #1379101-1
COV+LEV MQS 18W 90DEG BLK





TE Part #1379100-2
COV+LEV MQS 18W 0DEG WHI

TE Part #K1151027
Relay-ECS 26-56-99-907



TE Part #185402-1
MODULAR RELAY HOLDER



TE Part #929051-1
MQS ABDEKA M.HEB12P



TE Part #DTMH06-4SA
PLG, 4P, BLK, N, HI TEMP, A

Documents

Product Drawings
26W MQS COVER ASSY BLUE
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_185879-2_O.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_185879-2_O.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_185879-2_O.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications
Product Specification
English

Instruction Sheets
Instruction Sheet (non U.S.)
English