

ÖLFLEX® CLASSIC 415 CP

Screened, abrasion- and oil-resistente PUR control cable with reduced outer diameter

ÖLFLEX® 415 CP - PUR control cable, screened, for space-saving, oil- and abrasion resistant application in industrial machinery automation and appliances

Info

Thin and light, without inner sheath
EMC compliant copper screening



Interference signals



Oil-resistant



Mechanical resistance

Benefits

Space and weight-saving installations due to small cable diameters

Increased durability under harsh conditions thanks to robust PUR outer sheath

Resistant to contact with many mineral oil-based lubricants, diluted acids, aqueous alkaline solutions and other chemical media

Copper braiding screens the cable against
electromagnetic interference

Application range

Industrial machinery and machine tools

Measurement, control and electrical applications

Very suitable for oily wet areas within machinery and production lines that are subject to normal mechanical stress

Outdoor use is possible within the indicated operating temperature range

ÖLFLEX® CLASSIC 415 CP

Product features

High oil-resistance
Abrasion and notch-resistant
EMC-compliant
Low-adhesive surface
Resistant to hydrolysis and microbes

Norm references / Approvals

Core based on VDE 0812/0285
Outer sheath based on VDE 0250/0285

Product Make-up

Fine-wire, bare copper conductor
Core insulation: special PVC
Cores twisted in layers
Plastic foil wrapping
Tinned-copper braiding
Special polyurethane outer sheath (PUR)
Sheath colour: silver grey (RAL 7001)

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Core identification code:	Black with white numbers acc. to VDE 0293-1
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Minimum bending radius:	Occasional flexing: 20 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	Core/core: 4000 V Core/screen: 2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

Note

Unless otherwise specified, the product values shown are nominal values. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Copper price basis: EUR 150/100 kg; see catalogue appendix T17 for the application and definition of "Metal price basis" and "Metal index"

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging: Ring ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred packaging (e.g. 1 x 500 m drum or 5 x 100 m rings)

Photographs are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC 415 CP**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CLASSIC 415 CP				
1314000	2 X 0.5	5.8	36	45
1314001	3 G 0.5	6.1	43	59
1314002	3 X 0.5	6.1	43	59
1314003	4 G 0.5	6.5	49	83
1314004	4 X 0.5	6.5	49	83
1314005	5 G 0.5	7	57	96
1314006	5 X 0.5	7	57	96
1314007	7 G 0.5	7.5	69	136
1314008	7 X 0.5	7.5	69	136
1314010	12 G 0.5	9.9	104	200
1314011	12 X 0.5	9.9	104	200
1314012	18 G 0.5	11.5	141	275
1314013	18 X 0.5	11.5	141	275
1314014	25 G 0.5	13.4	211	350
1314015	25 X 0.5	13.4	211	350
1314017	2 X 0.75	6.2	43	56
1314018	3 G 0.75	6.5	52	70
1314019	3 X 0.75	6.5	52	70
1314020	4 G 0.75	7	61	95
1314021	4 X 0.75	7	61	95
1314022	5 G 0.75	7.7	72	130
1314023	5 X 0.75	7.7	72	130
1314024	7 G 0.75	8.3	89	168
1314025	7 X 0.75	8.3	89	168
1314026	12 G 0.75	10.9	138	232
1314027	18 G 0.75	12.7	211	315
1314028	25 G 0.75	14.8	280	435
1314029	25 X 0.75	14.8	280	435
1314032	2 X 1	6.5	51	84
1314033	3 G 1	6.8	62	110
1314034	3 X 1	6.8	62	110
1314035	4 G 1	7.3	74	130
1314036	4 X 1	7.3	74	130

Last Update (23.08.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

**ÖLFLEX® CLASSIC 415 CP**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1314037	5 G 1	8.1	88	156
1314038	5 X 1	8.1	88	156
1314039	7 G 1	8.8	112	192
1314040	7 X 1	8.8	112	192
1314041	12 G 1	11.5	185	285
1314042	18 G 1	13.9	268	395
1314043	25 G 1	15.9	354	656
1314046	2 X 1.5	7.1	65	97
1314047	3 G 1.5	7.5	82	125
1314048	3 X 1.5	7.5	82	125
1314049	4 G 1.5	8.2	100	165
1314050	4 X 1.5	8.2	100	165
1314051	5 G 1.5	8.9	119	193
1314052	5 X 1.5	8.9	119	193
1314053	7 G 1.5	9.9	154	245
1314054	7 X 1.5	9.9	154	245
1314055	12 G 1.5	13	268	365
1314056	18 G 1.5	15.6	373	553
1314057	25 G 1.5	17.9	530	734
1314058	34 G 1.5	20.8	683	944
1314061	3 G 2.5	8.9	118	188
1314062	4 G 2.5	9.9	147	236
1314063	5 G 2.5	11	176	270
1314064	7 G 2.5	11.9	253	340
1314065	12 G 2.5	16	355	589
1314066	18 G 2.5	19	569	978
1314067	25 G 2.5	22.2	827	1358
1314068	4 G 4	11.6	248	305
1314070	7 G 4	14.4	355	500
1314071	4 G 6	14.2	343	440
1314073	7 G 6	17	505	672
1314074	4 G 10	17.2	535	710
1314075	4 G 16	20.2	800	1050
1314076	4 G 25	25.1	1075	1570

Last Update (23.08.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet:
PN 0456 / 02_03_16



ÖLFLEX® CLASSIC 415 CP

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1314077	4 G 35	28	1576	2070

Last Update (23.08.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16