



Passive Components > Resistors > Potentiometers



Resistance Value: 10K Ω
Element Type: Carbon
Passive Component Tolerance: 20 %
Power Rating: .4 W
Product Terminates To: Wire

Features

Product Type Features

Rotary Turn Type	Single Turn
Element Type	Carbon
Sealing Option	Not Sealed

Configuration Features

Number of Turns	1
Sections	Dual
Adjustment Location	Side
Adjustment Method	Shaft

Electrical Characteristics

Resistance Value	10K Ω
Passive Component Tolerance	20 %
Power Rating	.4 W
Resistance Class	1k Ω – 1M Ω

Body Features

Shaft Style	Flatted
Product Orientation	Right Angle

Termination Features

Product Terminates To	Wire
-----------------------	------



Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Dimensions

Passive Component Dimensions	25.2 x 20.4 mm
Shaft Size	6.35 x 50 mm

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

27ESA103MMF50N

10K ohm, Carbon, 20 %, .4 W, Terminates To Wire, Panel Mount, 25.2 x 20.4 mm, Dual, Side Adjustment, 6.35 x 50 mm Shaft, Right Angle, Citec 23



TE Part # 1624213-2
[23SE 10KB 6.35X50FL B7 CAT](#)



TE Part # 1623763-2
[23E 100KA 6.35X50FL B7 CAT](#)



TE Part # 1623760-2
[23E 10KA 6.35X50FL B7 CAT](#)



TE Part # 1624139-2
[23E 4K7A 6.35X50FL B7 CAT](#)



TE Part # 1624202-2
[23SE 10KA 6.35X50FL B7 CAT](#)

Also in the Series | [Citec 23](#)



[Potentiometers\(81\)](#)

Customers Also Bought



TE Part #5-1393766-7
[R10-E1Y4-V700=R10](#)



TE Part #9-1437622-2
[KPN500B1/4=KNOB BLK W/POINTER](#)




TE Part #1-1393143-2
[27E129=SOCKET,R10,16,PC,PHEN](#)



TE Part #2-111623-7
[024 2MM CTR 30DP FT](#)



TE Part #EN7993-000
[CI-INT-1222-S-010](#)



TE Part #CAT-C339-SM1A
[SMD Power Resistor: 7 Watt, 0.10-500 Ohm](#)



TE Part #1622176-1
[LR0204 1% 18K](#)



TE Part #5748952-1
[AMP III PLUG 15P RA 590 FFSCRLK](#)



Documents

Product Drawings

27E DUAL 10KA 6.35X50FL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1624176-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1624176-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1624176-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Spindle Operated Potentiometers - Type 23 series - Tyco Electronics Passives

English