




OSLON® P1616 Broadband MicroOSLON

ILM-IP01-BBEM-SC201-WIR200

At the heart of each MicroOSLON is the OSLON P1616 Broadband LED from OSRAM Opto Semiconductors. The OSLON P1616 LED emits broadband infrared light in wavelengths ranging from 650 to 1,050 nanometres (nm). It is ideal for near-infrared spectroscopy, which can be used to assess food, medicine and even measure body fat. The OSLON P1616 created a whole new field of compact, robust and low-cost sensing technology that did not exist before, making it possible to integrate spectrometers directly into mobile devices like smartphones and tablets. MicroOSLONs are compact, powerful LED light sources built on aluminium substrates for optimal thermal management. Available with 200mm wires as standard.



CONTENTS

Applications	page 2	Secondary Optics Options	page 6
Technical Features	page 2	Heatsink Options	page 6
Product Options	page 3	Power Supply Options	page 7
Minimum and Maximum Ratings	page 3	Thermal Interface Material Options	page 7
Accessories	page 4	Assembly Information	page 8
Technical Drawings	page 5	Important Information and Precautions	page 8
LED Radiation Diagram	page 5	Safety Information	page 9
Relative Spectral Emission	page 6		

APPLICATIONS

- » Infrared Spectroscopy
- » Medical

- » Wearables

TECHNICAL FEATURES

LED Family	OSLON P1616
Lifetime	Up to 50,000 hours lifetime to 70% of original brightness
Mounting	Mounting holes using M3 screws allow easy installation
Dimensions	(L x W x H) 11 x 11 x 2.41mm
Wiring	Available with 200mm connecting wires
Secondary Optics	A secondary optic can be fitted. Suitable options on page 6 or visit our website for a full range
Heatsinks	Currently there are no Heatsink options available for the MicroOSLONs
Power Supply	4-75W dimming and non-dimming. Suitable options on page 9 or visit our website for a full range
Chain	MicroOSLONs can be linked together to produce longer chains
Current Range	500mA
Thermal Resistance	??K/W

PRODUCT OPTIONS

ILS Part Number	Wavelength	Typical Power W § At 350mA	Forward Voltage	Flux † at 350mA	Radiance Angle	Relevant OSRAM LED Data
ILM-IP01-BBEM-SC201-WIR200.	650-1050nm	1.48W	2.95-3.5V	74mW	120° (±60°)	SFH4737

Due to the special conditions of the manufacturing processes of LEDs, the typical data of technical parameters can only reflect overall statistical figures, and do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data.

§ Tolerance +/- 10%

† Measured with 20mS 350mA pulse at 85 °C

MINIMUM AND MAXIMUM RATINGS

ILS Part Number	Operating Temperature at Tc-Point [°C]	Storage Temperature [°C]	Forward Current per Module [mA]	Reverse Voltage [Vdc]
ILM-IP01-BBEM-SC201-WIR200.	-40 °C - 85 °C	-40 °C - 85 °C	500mA	Not designed for reverse operation

Exceeding maximum ratings for operating and storage temperature will reduce expected life time or destroy the LED module.

Exceeding maximum ratings for operating voltage will cause hazardous overload and will likely destroy the LED module.

The temperature of the LED module must be measured at the Tc-Point according to EN60598-1 in a thermally constant status with a temperature sensor or a temperature sensitive label.


ACCESSORIES

Secondary Optics Options



LEDiL precision-engineered lenses and reflectors allow for rapid deployment of all types of light fixtures, including street lights, wall-wash, high-bay, sconces, emergency beacons, parking garage/low-bay, MR and AR downlights, and dock lights. Precision-engineered for maximum efficiency and durability, LEDiL lenses and reflectors are released alongside the latest products from our LED suppliers. Suitable options on [page 6](#) or visit [our website](#) for a full range.

Heatsinks



ILS has a series of aluminium alloy heatsinks to be used with our standard range of PowerStars and PowerClusters. These heatsinks are supplied with fixing screws for the light engine and for fixing to a base plate. They also come with thermal interface material (TIM) attached to the top surface. Suitable options on [page 6](#) or visit [our website](#) for a full range.


Power Supplies

ILS has a comprehensive range of standard power supplies. The table below shows the total number of ILS products each power supply can drive. Additional power supplies are being introduced so please call us or [check our website](#) for the latest offering. Suitable options on [page 7](#)



Thermal Interface Material (TIM)


ILS has produced a range of high-performance, cost effective thermal interface materials to perfectly match their standard products. Our product fills the air pockets between the two surfaces, forming a continuous layer to conduct heat away from the LED to the heatsink. ILS offers TIM in three options – double sided adhesive, single sided adhesive and non adhesive. Suitable options on [page 7](#) or visit [our website](#) for a full range.




TECHNICAL DRAWINGS (MM)

Coming Soon

RADIATION OF SINGLE LED



RELATIVE SPECTRAL EMISSION



SECONDARY OPTICS OPTIONS

Part Number	Beam	Size	Height	Family	FWHM	Material	Colour	Fastening
FP11001_LISA2-M-PIN	Medium	10mm	6.7mm	LISA 2	20	PMMA +PC	Black	Pin
FP11002_LISA2-W-PIN	Wide	10mm	6.7mm	LISA 2	35	PMMA +PC	Black	Pin
FP11003_LISA2-WW-PIN	Wide	10mm	6.7mm	LISA 2	45	PMMA +PC	Black	Pin
FP11047_LISA2-RS-PIN	Real Spot	10mm	6.7mm	LISA 2	19	PMMA +PC	Black	Pin
FP11081_LISA2-M-CLIP	Medium	10mm	6.7mm	LISA 2	20	PMMA +PC	Black	Clip
FP11082_LISA2-W-CLIP	Wide	10mm	6.7mm	LISA 2	35	PMMA +PC	Black	Clip
FP11083_LISA2-WW-CLIP	Wide	10mm	6.7mm	LISA 2	45	PMMA +PC	Black	Clip
FP11084_LISA2-RS-CLIP	Real Spot	10mm	6.7mm	LISA 2	19	PMMA +PC	Black	Clip
FP11120_LISA2-O-CLIP	Oval	10mm	6.7mm	LISA 2	45x20	PMMA +PC	Black	Clip
FP11124_LISA2-O-PIN	Oval	10mm	6.7mm	LISA 2	45x20	PMMA +PC	Black	Pin
FP11429_LISA2-WWW-PIN	Wide	10mm	6.7mm	LISA 2	80	PMMA +PC	Black	Pin
FP11431_LISA2-WWW-CLIP	Wide	10mm	6.7mm	LISA 2	80	PMMA +PC	Black	Clip
FP11957_LISA2-WWW-PIN	Wide	10mm	6.7mm	LISA 2	80	PMMA +PC	Black	Pin














[Click here to visit our website for our latest range](#)

HEATSINK OPTIONS

Currently there are no Heatsink options available for the MicroOSLONs.

[Click here to visit our website for our latest range](#)

POWER SUPPLY OPTIONS

	ILS Driver Part Number	Rating	Current	LED Driver Voltage	Dimming
	IZC035-008F-5065C-SA	8W	350mA	3-36V	None
	IZC035-017F-0067A-SA	17W	350mA	6-48V	None
	IZC035-018T-9500A-SX	18W	350mA	15-52V	None
	IZC050-018T-9500A-SX	18W	500mA	9-36V	None
	IZC045-040A-9266C-SA	40W	450mA	30-89V	None
	IZCVAR-040M-9020C-SAL	40W	350mA, 500mA, 600mA, 700mA, 900mA, 1050mA	350mA 2-100V, 500mA 2-80V, 600mA 2-67V, 700mA 2-57V, 900mA 2-45V, 1050mA 2-40V	None
	OTi-DALI-10/220-240/700-NFC	10W	150-700mA	2.5-45V	None
	OTE-13/220-240/350-PC	13W	350mA	18-38V	None
	OT-FIT-15/220-240/500-LT2-LP	15W	150-500mA	15-50V	None
	OTi-DALI-15/220-240/1A0-LT2	15W	150-1050mA	7.5-54V	None
	OT-20/170-240/800-4DIMLT2-G2-CE	20W	200-1050mA	10-38V	None
	ELEMENT-LD-20/220-240/500	20W	500mA	21-42	None
	OT-FIT-30/220-240/700-CS-G2	30W	500-700mA	23-42V	None

[Click here to visit our website for our latest range](#)

THERMAL INTERFACE MATERIAL OPTIONS

Non Adhesive

LA-TIM-MICRO-2A

Other sizes are available, including customised parts

[Click here to visit our website for our latest range](#)

ASSEMBLY INFORMATION

- » The mounting of the PowerStar has to be on a metal heatsink.
- » In order to optimise the thermal management, the metal surface needs to be clean (dirt and oil free) and planar for the best contact with the LED module. A thermal grease or heat transfer material is highly recommended.

IMPORTANT INFORMATION AND PRECAUTIONS



The LED module's LED, when powered up, is very bright. Thus it is advised that you do not look directly at it. Turn the LED module away from you and do not shine into the eyes of others.



LED module, when operated, can reach high temperatures thus there is risk of injury if they are touched.



LED module's will overheat in operation if not attached to a suitable heatsink. Overheating can cause failure or irreparable damage.



DO NOT HOT PLUG ON LED SIDE OF POWER SUPPLY.



Do not operate LED module's with a power supply with unlimited current. Connection to constant voltage power supplies that are not current limited may cause the LED module's to consume current above the specified maximum and cause failure or irreparable damage.



DO NOT TOUCH or PUSH on the LED as this can cause irreparable damage.

SAFETY INFORMATION



The LED module itself and all its components must not be mechanically stressed.



Assembly must not damage or destroy conducting paths on the circuit board.



The mounting of the module is carried out by attaching it at the mounting holes. Metal mounting screws must be insulated with synthetic washers to prevent circuit board damage and possible short circuiting.



To avoid mechanical damage to the connecting cables, the boards should be attached securely to the intended substrate. Heavy vibration should be avoided.



Observe correct polarity! Depending on the product, incorrect polarity will lead to emission of red or no light. The module can be destroyed!



Pay attention to standard ESD precautions when installing the LED modules.



The LED modules, as manufactured, have no conformal coating and therefore offer no inherent protection against corrosion. Damage by corrosion will not be accepted as a materials defect claim. It is the user's responsibility to provide suitable protection against corrosive agents such as moisture and condensation and other harmful elements.



For outdoor usage, a housing is definitely required to protect the board against environmental influences. The design of the housing must correspond to the IP standards in the application. It is also the responsibility of the user to ensure any housings or modifications keep the T_c junction temperature to within stated ranges.



To also ease the luminaire/installation approval, electronic control gear for LED or LED modules should carry the CE mark and be ENEC certified. In Europe the declarations of conformity must include the following standards: CE: EC 61374-2-13, EN 55015, IEC 61547 and IEC 61000-3-2 - ENEC: 61374-2-13 and IEC/EN 62384.



The evaluation of eye safety occurs according to the standard IEC 62471:2006 ("photobiological safety of lamps and lamp systems"). Within the risk grouping system of this CIE standard, the LED specified in this datasheet falls into the class "moderate risk" (exposure time 0.25s). Under real circumstances (for exposure time, eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. As is also true when viewing other bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment and even accidents, depending on the situation.

FURTHER INFORMATION

The values contained in this datasheet can change due to technical innovation. Any such changes will be made without separate notification.

If you require further assistance or have a specific or custom enquiry, please contact the ILS team via email or phone. Alternatively please visit our website for more product information and to see our full ranges.



Unit 2, Berkshire Business Centre,
Berkshire Drive, Thatcham,
Berkshire, RG19 4EW
+44 (0)1635 294606

info@i-led.co.uk

<https://i-led.co.uk>

ABOUT ILS

ILS offers a high level of technical skill, professionalism and commercial understanding to companies requiring market-leading optoelectronics solutions. Offering conceptual advice, electronics design and manufacturing capability, we use high quality production resources both in-house and in Asia, providing project support from prototyping to mass production. We also understand the need to provide cost-effective solutions and we do so using high quality components to ensure that the end product's reliability and quality is uncompromised. Apart from LEDs in the visible spectrum, we have a wide range of **Infrared**, **UV LEDs**, **UV tubes**, and lasers.

ILS is a division of **Intelligent Group Solutions Ltd (IGS)** a well-established respected industry leading Optoelectronics solutions provider. Much of IGS' business comes from providing semi-custom or custom products both in component and sub-assembly form, and from providing design support and prototyping within the European market place. We can deliver production displays to wherever in the world that the customer's manufacturing or assembly is being undertaken.

INTELLIGENT GROUP SOLUTIONS DIVISIONS

