



Connectors > Circular Connectors > Standard Circular Connectors



Number of Positions: 3

Connector System: Cable-to-Cable

Polarization Code: A

Number of Power Positions: 0

Number of Signal Positions: 0

Features

Product Type Features

Prewired	No
Connector System	Cable-to-Cable
Circular Connector Type	Receptacle

Configuration Features

Keying & Polarized Position Locations	Normal
Number of Positions	3
Number of Power Positions	0
Number of Signal Positions	0

Contact Features

Circular Connector Contact Type	Socket
---------------------------------	--------

Mechanical Attachment

Polarization Code	A
-------------------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1-2213427-1  
NECTOR M 1FI SKT ASSEMBLY, FREE HANG




TE Part # 2213395-1  
NECTOR M FI PIN ASSEMBLY, FH (UL)


Customers Also Bought




TE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING



TE Part #281934-2  
SINGLE WIRE SEAL



TE Part #114017-ZZ  
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D48-ST273  
DEUTSCH Solid Contacts



Documents

Product Drawings

NECTOR M FI SKT ASSEMBLY, FH (UL)

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2213427-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2213427-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2213427-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.