

Datasheet

RS Pro Round Fixed Height Mount, 160mm, Rubber, Galvanised Steel 4000kg, M20

RS Stock No: **442-599**



Product Details

RS Pro round anti-vibration mount has rubber and galvanised steel construction for long life durability. It has a static load capacity of 4000 kg and thread size of M20. A series of machine mounts specifically designed for applications where strict demands are imposed on effective vibration damping and the reduction of noise emitted from machinery and equipment. This heavy duty machine mount consists of a threaded pressure plate that can be adjusted by an integrated levelling bolt. The design rests on a steel chassis and a thick rubber damping element that withstands most types of grease, acid, oil and cooling emulsion normally used in industry. A tried and tested design with good levelling characteristics makes these machine mounts the natural choice for the majority of machine types used in industry.

Features and Benefits

- Precision installation of machine tools, printing presses and other industrial machines
- Absorbs vibration and reduces noise levels
- Galvanised steel with oil resistant rubber base
- Accurate height adjustment with fine pitch screw
- Highly resistant to horizontal forces
- Capable of handling heavier loads than the general duty types



ENGLISH

Specifications:

Foot Shape	Round
Material	Rubber
Metalwork	Galvanised Steel
Mounting Type	Screw-In
Type	Anti-Vibration Mount
Diameter	160 mm
Overall Height	69 mm
Static Load Capacity	4000 kg
Thread Size	M20