




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Keyed**
Mating Retention: **With**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Columns	3
Number of Loaded Positions	3
Contacts Preloaded	Yes
Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features



Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Layout	Inline
Wire Contact Termination Area Plating Material	Silver
Contact Mating Area Plating Material	Silver (Ag)
Contact Retention Within Housing	Without
Contact Current Rating (Max)	16 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Locking Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1971895-3
3P, RAST 5 Tab Header, THV




TE Part # 1-2178661-3
MULTIFIT MK2 ASSY3P

Also in the Series | RAST 5 IDC Connectors




Connector Contacts(12)



Crimp Terminal Housings(39)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(417)



Power Contacts(3)



Rectangular Power Connectors(481)



Standard Edge Connectors(31)




Wire-to-Board Headers & Receptacles (417)


Customers Also Bought



TE Part #1862006-5
STD PW TIMER CONTACT



TE Part #336075-3
250 FASTON,REC.,20-16 AWG,PTBR



TE Part #336076-3
250 FASTON,E-SPRING REC.,17-14 AWG,PTBR



TE Part #1534073-2
MULTIFIT MK2 ASSY2P



TE Part #2298752-9
AMP MONO-SHAPE PCB CONN LONG 9 POS



TE Part #2293382-5
AMP MONO-SHAPE TAB CONN 5P.



TE Part #2178571-3
STANDARD TIMER HSG 4P



TE Part #1747050-1
GRACE INERTIA CONNECTOR 7.92 2POS PLUG H



TE Part #1534072-3
MULTIF.ASSY MK2 3POS,AR



TE Part #7-1740533-3
AMP DUOPLUG POW CONN. 3POS W.PCB LOCKING

Documents

Product Drawings

MULTIFIT MK2 ASSY3P

English

MULTIFIT MK2 ASSY3P

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1534073-3_K.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_1-1534073-3_K.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1534073-3_K.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[VDE Certificate](#)

English

[VDE Certificate](#)

English

[VDE Certificate](#)

English