





VBA10/11A, Booster Regulator VBA11A-02GLS

Datasheet







- Service life increased.
- Noise reduced.
- Condensation reduced.
- Reliability improved.



Pneumatic booster regulator, handle operated

Standard specifications

Body Size	11A (1/4, Handle-operated Type, Pressure Increase Ratio 2 to 4 Times)
Thread Type	Rc (PT)
Option	GLS (Pressure Gauge [2 pcs.] + Elbow High Noise Reduction Silencer)
Semi-standard	Standard
-	Compressed Air
Maximum operating pressure	1.0 MPa
Minimum operating pressure	0.1 MPa
Proof pressure	3.0 MPa
Set pressure range	0.2 to 2.0 MPa
Port size	Rc 1/4
Pressure increase ratio	2 to 4 times
Pressure adjustment mechanism	Handle-operated with relief mechanism
Max. Flow rate (l/min (ANR))	70 (l/min (ANR))
Supply pressure range (MPa)	0.1 to 1.0 MPa
Pressure gauge port size (Rc) (IN/OUT: 2 locations)	Rc 1/8
Installation	Horizontal
Lubrication	Grease (Non-lube)
Weight	0.928 Kg



Additional information

Catalogue	VBA-VBAT_Dd_EU.pdf
Operation manuals	OM_VBA-OM-L007-E_EN.pdf OM_VBA-MM-N016-E_EN.pdf OM_VBA10A_N010EN-E.pdf