

Double coax A/V cable(7492481)



Part NO: RGW-1597-2

Product Code: Double coax A/V cable(7492481)

Product Description

Application:

For communication and signal control systems.

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

S-video+2 Audio Cables

	Cable Construction	
Conductor	A (S-video)	B (2 Audio Cables)
Material	Bare Copper	Bare Copper
Construction	0.37±0.008	0.10±0.003×18
Standard Dia. (mm)	0.37	0.49
Insulation Layer	Foam PE	Foam PE
Thickness(mm)	0.56	0.50
Insulation Dia. (mm)	1.5±0.1	1.50±0.1
Insulation Color:	Natural	Yellow ; Red
Spiral	Bare Copper	Bare Copper
Construction(mm)	0.10±0.003x40	0.10±0.003x40
Separation	one core use Pet Mylar	-----
	another core use Blue Al fo	-----
Jacket	PVC	PVC
Thickness(mm)	0.6	0.6
Dia.(±0.15mm)	3.1×5.3	2.9/2.9
Jacket Color	BLACK	BLACK
Whole Jacket dia.	3.1×11.7	


Marking

Double Coax A/V Video 2 x 0.37 + 2 x 0.14mm2 PVC +Meter marking


PACKAGING

25M Coil

4Pcs/Box



Design



Electrical Characteristics

Max.Conductor DC Resistance at 20℃ (Ω /Km)

A	172
B	132
Insulation DC Resistance at 20℃ (M Ω *KM)	>500
Rated Temperature(℃)	-20 to +70
Rated Voltage(V)	30
Capacitance(pF/m) (Audio Cable)	100pF/m

Attenuation at 20℃ (dB/100m) (+/-15%)

5 MHz	4
10 MHz	5.6
20 MHz	8.4
50 MHz	13.9
100 MHz	19.8

Label for each coil

Product label

Double coax A/V cable
Black
25M
RoHS(2002/95/EC) Compliant
WW/YY

RS label

7492481
25M
Made in China



Revision History

A0-1

Date: 2011-11-29

Page : 1 of 1