






Snap Rivets

SR/SRVO

Material: UL94 V2 Nylon 6, RMS-52

Material: UL94 V0 Nylon 6/66, RMS-103



Part Number			Hole Ø "G"	Extraction Force kg Typ.	Total Holding Thickness "F"	Dimensions (mm)					Fig. No.	Std Pack Qty
Black	White	Black				"A" Ø	"B"	"C"	"D" Ø	"E"		
SR-2024B	SR-2024W	SRVO-2024B	2.1 - 2.2	3	0.6 - 1.2	4.2	1.2	2.4	2	2.8	1	1000
SR-2032B	SR-2032W	SRVO-2032B	2.1 - 2.2	3	1.3 - 2	4.2	1.2	3.2	2	3.8	1	1000
SR-2040B	SR-2040W	SRVO-2040B	2.1 - 2.2	3	2.1 - 2.8	4.2	1.2	4	2	5.5	1	1000
SR-2048B	SR-2048W	SRVO-2048B	2.1 - 2.2	3	2.9 - 3.6	4.2	1.2	4.8	2	5.5	1	1000
SR-2056B	SR-2056W	SRVO-2056B	2.1 - 2.2	3	3.7 - 4.4	4.2	1.2	5.6	2	7.2	1	1000
SR-2064B	SR-2064W	SRVO-2064B	2.1 - 2.2	3	4.4 - 5	4.2	1.2	6.4	2	7.1	1	1000
SR-2632B	SR-2632W	SRVO-2632B	2.7 - 2.8	5	1 - 2	5	1.4	3.2	2.6	4.5	1	1000
SR-2642B	SR-2642W	SRVO-2642B	2.7 - 2.8	5	2 - 3	5	1.4	4.2	2.6	4.5	1	1000
SR-2648B	SR-2648W	SRVO-2648B	2.7 - 2.8	5	2.7 - 3.6	5	1.4	4.8	2.6	6.1	1	1000
SR-2655B	SR-2655W	SRVO-2655B	2.7 - 2.8	5	3.4 - 4.3	5	1.4	5.6	2.6	6.1	1	1000
SR-2664B	SR-2664W	SRVO-2664B	2.7 - 2.8	5	4.3 - 5.2	5	1.4	6.4	2.6	7.8	1	1000
SR-2672B	SR-2672W	SRVO-2672B	2.7 - 2.8	5	5.1 - 6	5	1.4	7.2	2.6	7.8	1	1000
SR-3035B	SR-3035W	SRVO-3035B	3.1 - 3.2	8	1 - 2	6.4	1.6	3.5	3	5.1	1	1000
SR-3045B	SR-3045W	SRVO-3045B	3.1 - 3.2	8	2 - 3	6.4	1.6	4.5	3	6.1	1	1000
SR-3055B	SR-3055W	SRVO-3055B	3.1 - 3.2	8	3 - 4	6.4	1.6	5.6	3	6.1	1	1000
SR-3065B	SR-3065W	SRVO-3065B	3.1 - 3.2	8	4 - 5	6.4	1.6	6.5	3	7.1	1	1000
SR-3075B	SR-3075W	SRVO-3075B	3.1 - 3.2	8	5 - 6	6.4	1.6	7.5	3	9	1	1000
SR-3080B	SR-3080W	SRVO-3080B	3.1 - 3.2	8	5.5 - 6.5	6.4	1.6	8	3	9	1	1000
SR-3090B	SR-3090W	SRVO-3090B	3.1 - 3.2	8	6.5 - 7.5	6.4	1.6	9	3	11	1	1000
SR-3100B	SR-3100W	SRVO-3100B	3.1 - 3.2	8	7.5 - 8.5	6.4	1.6	10	3	11	1	1000
SR-3535B	SR-3535W	SRVO-3535B	3.6 - 3.7	12	1.2 - 2.1	6.4	1.6	3.5	3.5	5.1	2	1000
SR-3545B	SR-3545W	SRVO-3545B	3.6 - 3.7	12	2.1 - 3	6.4	1.6	4.5	3.5	6.1	2	1000
SR-3550B	SR-3550W	SRVO-3550B	3.6 - 3.7	12	2.7 - 3.6	6.4	1.6	5	3.5	6.1	2	1000
SR-3555B	SR-3555W	SRVO-3555B	3.6 - 3.7	12	3 - 4	6.4	1.6	5.6	3.5	7.1	2	1000
SR-3560B	SR-3560W	SRVO-3560B	3.6 - 3.7	12	3.7 - 4.6	6.4	1.6	6	3.5	7.1	2	1000
SR-3570B	SR-3570W	SRVO-3570B	3.6 - 3.7	12	4.5 - 5.5	6.4	1.6	7.2	3.5	9	2	1000
SR-3580B	SR-3580W	SRVO-3580B	3.6 - 3.7	12	5.5 - 6.5	6.4	1.6	8	3.5	9.1	2	1000
SR-4050B	SR-4050W	SRVO-4050B	4.1 - 4.2	20	2.5 - 3.5	8	1.8	5	4	7.1	2	1000
SR-4060B	SR-4060W	SRVO-4060B	4.1 - 4.2	20	3.5 - 4.5	8	1.8	6	4	7.1	2	1000
SR-4070B	SR-4070W	SRVO-4070B	4.1 - 4.2	20	4.5 - 5.5	8	1.8	7.2	4	9	2	1000
SR-4080B	SR-4080W	SRVO-4080B	4.1 - 4.2	20	5.5 - 6.5	8	1.8	8	4	9	2	1000
SR-4090B	SR-4090W	SRVO-4090B	4.1 - 4.2	20	6.5 - 7.5	8	1.8	9	4	11	2	1000
SR-4100B	SR-4100W	SRVO-4100B	4.1 - 4.2	20	7.5 - 8.5	8	1.8	10	4	11	2	1000
SR-4120B	SR-4120W	SRVO-4120B	4.1 - 4.2	20	9 - 10.5	8	1.8	12	4	14	2	1000
SR-5045B	SR-5045W	SRVO-5045B	5.1 - 5.2	25	1.5 - 2.5	9	2.2	4.5	5	6.5	2	1000
SR-5055B	SR-5055W	SRVO-5055B	5.1 - 5.2	25	2.5 - 3.5	9	2.2	5.6	5	6.5	2	1000
SR-5065B	SR-5065W	SRVO-5065B	5.1 - 5.2	25	3.5 - 4.5	9	2.2	6.5	5	8.5	2	1000
SR-5075B	SR-5075W	SRVO-5075B	5.1 - 5.2	25	4.5 - 5.5	9	2.2	7.5	5	8.5	2	1000
SR-5085B	SR-5085W	SRVO-5085B	5.1 - 5.2	25	5.5 - 6.5	9	2.2	8.5	5	10.5	2	1000
SR-5095B	SR-5095W	SRVO-5095B	5.1 - 5.2	25	6.5 - 7.5	9	2.2	9.5	5	10.5	2	1000
SR-5105B	SR-5105W	SRVO-5105B	5.1 - 5.2	25	7.5 - 8.5	9	2.2	10.5	5	12	2	1000
SR-6060B	SR-6060W	SRVO-6060B	6.1 - 6.2	30	2.5 - 4	12	2.5	6	6	9	2	1000
SR-6080B	SR-6080W	SRVO-6080B	6.1 - 6.2	30	3.5 - 5.5	12	3	8	6	10	2	1000