

Datasheet

RS Pro NPI75C Series Wire-wound SMD Inductor 22 μ H \pm 20% Wire-Wound 1.5A Idc

RS Stock No: **740-9659**



Product Details

RS Pro wire-wound SMD inductor offers inductance of 22 μ H and withstands DC current up to 1.5 A. It works with DC-DC converters and DC-AC inverters. This compact filter is suitable for both flow and reflow soldering.

Features and Benefits

- High current, small size (up to 4 amps)
- Surface mountable construction
- High inductance (up to 680 μ H)
- Suitable for use in DC/DC converters, DC/AC inverters
- Lead free compatible

Specifications:

Inductor Construction	Wire Wound
Shielded	No
Depth	7 mm
Dimensions	7.8 x 7 x 5 mm
Height	5 mm
Length	7.8 mm
Maximum DC Current	1.5 A
Maximum DC Resistance	110 mΩ
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Tolerance	±20%
Inductance	22 μH
Package/Case	75
Package Type	Tape & Reel