



Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold (Au)**
Contact Base Material: **Copper Alloy**
Circuit Application: **Power**
Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.762 µm[30 µin]
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

--	--



Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CROWN EDGE




[Card Edge Power Connectors\(30\)](#)



[Connector Contacts\(1\)](#)




[Power Contacts\(1\)](#)



[Standard Edge Connectors\(2\)](#)

Customers Also Bought



TE Part #1623783-7
[SQM7 22K 5% \(METAL FILM\)](#)



TE Part #1571983-9
[GDH06STR04=DIP SWITCH](#)




TE Part #3-647502-4
[04P MTA100 HDR ASSY,SM,SN, LF](#)



TE Part #2214870-1
[MiniSAS HD 1x4 Rec Assy w/ weld](#)



TE Part #5-146281-3
[03 MODII HDR SRST B/A LF](#)



TE Part #2332208-3
[RECEPT ASSY, RA, 56 POS, SLIVER 2.0](#)



TE Part #1676285-3
[RN 0805 2K21 0.1% 10PPM 5KRL](#)



TE Part #1676241-2
[RN 0805 1K74 0.1% 10PPM 1KRL](#)



TE Part #5-146256-1
[02 MODII HDR DRST B/A .100CL LF](#)



TE Part #5767054-1
[MICT,RECPT,38,ASSY,PDNI](#)

Documents

Product Drawings

[284-0492-11000=TA CONN,SKT](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1766354-1_C.2d_dxf.zip](#)

English

[3D PDF](#)



3D

Customer View Model

[ENG_CVM_CVM_1766354-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1766354-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English