

Through-type terminals with screw terminal Terminal size 16.0 mm<sup>2</sup>  
Terminal width 12.0 mm Color gray



Model	
product brand name	ALPHA
product designation	ALPHA FIX terminal blocks
design of terminal / terminal levels internally linked	No
General technical data	
terminal contact spacing	12 mm
operating voltage / rated value	1 000 V
Protection class	
combustibility class acc. to UL 94	V0
Main circuit	
operational current / rated value	76 A
Appearance	
color	beige
Product details	
product component / required / end cover plate	Yes
Number	

number of terminal levels	1
number of terminal points / per terminal level	2

### Connections

stripped length	14 mm
connectable conductor cross-section / solid	<ul style="list-style-type: none"> <li>• minimum 1.5 mm<sup>2</sup></li> <li>• maximum 25 mm<sup>2</sup></li> </ul>
connectable conductor cross-section / finely stranded	<ul style="list-style-type: none"> <li>• with core end processing / minimum 1.5 mm<sup>2</sup></li> <li>• with core end processing / maximum 16 mm<sup>2</sup></li> </ul>
tightening torque / with screw-type terminals	<ul style="list-style-type: none"> <li>• minimum 2.5 N·m</li> <li>• maximum 3 N·m</li> </ul>
type of electrical connection	<ul style="list-style-type: none"> <li>• 1 screw-type terminal</li> <li>• 2 screw-type terminal</li> </ul>
position / of the terminal	lateral

### Mechanical Design

height / with lowest-profile installation	55 mm
length	55.3 mm
fastening method	DIN rail 35 mm
net weight	30 g
material / of the insulating body	Thermoplast

### Environmental conditions

ambient temperature / during operation	<ul style="list-style-type: none"> <li>• minimum -25 °C</li> <li>• maximum 55 °C</li> </ul>
--	---

### Certificates

design tested acc. to type of protection / EEx e	No
--	----

<b>General Product Approval</b>	<b>Declaration of Con- formity</b>	<b>other</b>
---------------------------------	--	--------------



[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WH1000-0AK00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8WH1000-0AK00>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8WH1000-0AK00](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8WH1000-0AK00)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>