

FEATURES

- **2.5 m cable length:** Provides ample reach for connecting devices to power sources.
- **IEC C13W to CEE 7 connectors:** Ensures compatibility with a variety of equipment.
- **16 A current rating:** Supports high-power devices safely.
- **250 V voltage rating:** Suitable for standard voltage requirements.
- **Right angle plug:** Allows for space-saving installation in tight spaces.
- **Angled socket type:** Facilitates easy connection and disconnection.
- **Grey PVC jacket:** Offers durability and protection against environmental factors.

RS PRO 2.5 m Power Cable, IEC C13W to CEE 7

RS Stock No: 558-958



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO power cable is designed for reliable and efficient power transmission in various industrial and commercial environments. With a length of 2.5 metres, it offers flexibility and convenience for connecting equipment to power sources. The cable is equipped with an IEC C13W connector on one end and a CEE 7 connector on the other, making it suitable for a wide range of applications.

General Specifications

| | |
|-------------------|-------------|
| Connector Type A | IEC C13W |
| Connector Type B | CEE 7 |
| Jacket Colour | Grey |
| Mains Socket Type | Angled |
| Product Type | Power Cable |

Mechanical Specifications

| | |
|-----------------|--------------------|
| Cable Length | 2.5 m |
| Jacket Material | Polyvinyl Chloride |

Electrical Specifications

| | |
|-----------------|------------------|
| Current Rating | 16 A |
| Mains Plug Type | Right Angle Plug |
| Voltage | 250 V |

Approvals

| | |
|---------------------|---|
| Standards/Approvals | CCCs, CEBC, CSA, D, EAC, ENEC 11, FI, ICC, IMQ, JET, KEMA, KEUR, N, NF, OVE, PSE, RCM N10544, S, UL, VDA, |
|---------------------|---|

