



Connectors > Connector Accessories > Connector Backshells > AMPSEAL 16 Connectors Backshell



Connector Backshell Product Type: **Backshell**

Primary Product Material: **Nylon 6/6**

Body Orientation: **90**

Number of Positions: **4**

[All AMPSEAL 16 Connectors Backshell \(81\)](#)

Features

Product Type Features

Connector Backshell Product Type	Backshell
----------------------------------	-----------

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Primary Product Color	Black
Primary Product Material	Nylon 6/6

Housing Features

Body Orientation	90
------------------	----

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Serviceable	No
-------------	----



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMPSEAL 16



Automotive Connector Locks & Position Assurance(6)




Automotive Housings(239)




Connector Backshells(84)



Connector Seals & Cavity Plugs(10)



Data Connectivity Headers(2)



Data Connectivity Housings(3)



Other Automotive Connector Accessories(8)



Rectangular Backshells & Clamps(74)

Customers Also Bought



TE Part #CAT-L489-CH8172
LEAVYSEAL Connector Housings



TE Part #4828-007-8605
BKSHL, 86P, BLK, VERTICAL, DRCP



TE Part #0528-004-3805
BKSHL, 38P, BLK, PLG, RA



TE Part #DTP2P-BT-BK
BOOT, 2P, REC, ST, BLK



TE Part #DT06-6S-LC01
PLG, 6P, BLK, E, SEAL RET,DIN BKSHL ADPT



TE Part #HD10-9-96PE-B025
REC, 9P, BLK, E, PANEL, 16



TE Part #2-1703773-1
6POS,TAB 1.6X0.6,PIN HSG,ASSY



TE Part #HD10-3BT
BOOT, 3P, PLG/REC, ST, GRY



TE Part #DTM12P-DC
PROTECT CVR, 12P, REC, GRY, DTM

Documents



Product Drawings

Backshell,AS16,4P,90Deg,NC08,LP,Plug

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2035366-7_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2035366-7_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2035366-7_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English