



FUSE HOLDERS [Included LED Lamp • NEON Lamp]

※As soon as the element in the fuse is melted, you can recognize the condition by Indicator Lights.



THE WORKING OF A FUSE HOLDER



Usually Lights out
A wire fuse blows out → Lights up
(FHB-LN, FHB-LD, FHB-LNB, FHB-LDB)

★ORDER

FHB-LN	200PCS
Basic Type	Amount

TYPICAL SPECIFICATIONS


	FHB-LN	FHB-LD	FHB-SN	FHB-SD
Using Voltage	AC100V-220V	AC/DC12V-24V	AC100V-220V	AC/DC12V-24V
Current Capacity	Max.10A			
Fuse Dimension	6.4mm X 30mm Glass Tube			
Indicator Light	Neon	L.E.D.	Neon	L.E.D.
Material of Body / Cap	P.B.T. Plastic Glass-Fiber 30% / A.B.S. Plastic			
Temperature Rising (deg)	19℃~25℃			
Lamp Current	1±0.5mA	3±1mA	1±0.5mA	10±2mA
Terminal Conn. / Mounting	Soldering Type, Tab Terminal #187 / Lock Nut			
Weight	14g	14g	15g	15g

	FHB-LSN	FHB-LSD	FH-LNB	FH-LDB
Using Voltage	AC110V-220V	AC/DC12V-24V	AC110V-220V	AC/DC12V-24V
Current Capacity	Max.10A			
Fuse Dimension	6.4mm X 30mm Glass Tube			
Indicator Light	Neon	L.E.D.	Neon	L.E.D.
Material of Body / Cap	Polycarbonate		Phenol Resin	
Temperature Rising (deg)	19℃～25℃			
Lamp Current	1±0.5mA	5±0.5mA	1±0.5mA	1～4mA
Terminal Conn. / Mounting	By Soldering/By Lock Nut		By Soldering/By Lock Nut	
Weight	15g	15g	18g	18g


FUSE HOLDERS (Included LED Lamp • NEON Lamp)

※As soon as the element in the fuse is melted, you can recognize the condition by Indicator Lights.


- FHC-10KD
- FHC-10KN
- FHC-10K








- FHC-15D
- FHC-15N
- FHC-15




- FHC-15D 2P
- FHC-15N 2P
- FHC-15 2P




- FHC-15D 3P
- FHC-15N 3P
- FHC-15 3P



- FHC-30SD
- FHC-30SN
- FHC-30S



- FHC-30D
- FHC-30N
- FHC-30



■ WHEN FUSE BRAKED : RED LED IS ON.

- FHC-10KD • FHC-15KD • FHC-15D 2P,3P
- FHC-30SD • FHC-30D

■ WHEN FUSE BRAKED : RED NEON IS ON.



- FHC-10KN • FHC-15N • FHC-15N 2P,3P
- FHC-30SN • FHC-30N

■ WITHOUT LAMP

- FHC-10K • FHC-15 • FHC-15 2P,3P • FHC-30S
- FHC-30

■Din Rail


● FHC-15N,15D,15



Din Rail




《HOW TO INSTALL》



Frow Long Grip

● Fuse



- Fuse mounting Push the both caps of the fuse towards the opposite side.

■TYPICAL SPECIFICATIONS

	FHC-10KN	FHC-10KD	FHC-10K
Using Voltage	AC,DC100V-220V	AC,DC12V-28V	Max.250V
Current Capacity	Max.10A		
Fuse Dimension	6.4mm X 30mm Glass Tube		
Indicator Light	Neon	L.E.D.	Without Lamp
Material of Body	Phenol Resin		
Material of Cover	Polycarbonate		
Mounting	By Screw 4 X 10mm		
Temperature Rising (deg)	15℃~20℃		
Weight	36g	35g	35g

	FHC-15N	FHC-15D	FHC-15
Using Voltage	AC,DC100V-220V	AC,DC12V-28V	Max.250V
Current Capacity	Max.15A		
Fuse Dimension	6.4mm X 30mm Glass Tube		
Indicator Light	Neon	L.E.D.	Without Lamp
Material of Body	Phenol Resin		
Material of Cover	Polycarbonate		
Temperature Rising (deg)	15℃~20℃		
Lamp Current	About 0.5mA	1~4mA	
Weight	23g	23g	22g

■TYPICAL SPECIFICATIONS

	FHC-15N 2P, 3P	FHC-15D 2P, 3P	FHC-15 2P, 3P
Using Voltage	AC,DC100V-220V	AC,DC12V-28V	Max.250V
Current Capacity	Max.10A		
Fuse Dimension	6.4mm X 30mm Glass Tube		
Indicator Light	Neon	L.E.D.	Without Lamp
Material of Body / Cover	Phenol Resin / Polycarbonate		
Temperature Rising (deg)	15℃~20℃		
Lamp Current	About 0.5mA	1~4mA	
Terminal Conne. / Mounting	By Screw 4 X 8mm / By Screw 4 X 8~12mm		
Weight	48g (2P), 71g (3P)	48g (2P), 71g (3P)	46g (2P), 67g (3P)

	FHC-30SN,30SNE	FHC-30SD,30SDE	FHC-30S,30SE
Using Voltage	AC,DC100V-220V	AC,DC12V-24V	Max.440V
Current Capacity	Max.30A		
Fuse Dimension	10.5mm X 38mm Tube		
Indicator Light	Neon	L.E.D.	Without Lamp
Material of Body / Cover	Phenol Resin / Polycarbonate		
Temperature Rising (deg)	15℃(10A With Fuse), 12℃(5A With Fuse)		
Lamp Current	About 0.5mA	1~3mA	
Terminal Conne. / Mounting	By Screw 5 X 8mm / By Screw 5 X 8~12mm		
Weight	51g (SN), 58g (SNE)	51g (SD), 58g (SDE)	50g (S), 57g (SE)

●SPECIFICATIONS (All types are as follows:)

- Die-Electric Strength.....2000V 1Minute
- Insulating Strength.....500V 100Ω (D.C.Megger)

★ORDER

FHC-15N 200PCS
Basic Type Amount