

B-GEV 200K-TMR-SG

Pressed steel fixed castor, medium duty design, with top plate fitting, with dead man's brake, heavy duty wheel, with elastic solid rubber tyre, with cast iron wheel centre, non-marking, grey

EAN 4047526110253

ID 744226

Customs tariff number 87169090



Bracket: B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Wheel: GEV series

- tyre: high-quality elastic solid rubber in smooth rolling quality, hardness 65 Shore A, colour grey
- wheel centre: rugged grey cast iron, lacquered, colour silver

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -20 °C to +80 °C, temporarily up to +100 °C, reduced load capacity over +60 °C
- wheel centre is approximately 4 mm wider than the specified wheel width
- actuation path: approx. 10–12 mm
- operating angle: approx. 13°–15°
- actuation force: < 250 N
- braking force: > 500 N
- L or R must be added to the product code for left-handed and right-handed versions.

Technical data:

Wheel Ø (D)	☉	200 mm
Wheel width	⊥	50 mm
Load capacity at 4 km/h	⬆	600 kg
Load capacity (static)	⬆	1,500 kg
Bearing type	☉	ball bearing
Total height (H)	⌀	235 mm
Mounting type		top plate
Plate size	☐	140 x 110 mm
Bolt hole spacing	⊥	105 x 75–80 mm
Bolt hole Ø	⌀	11 mm
Temperature resistance min		-20 °C
Temperature resistance max		80 °C
Tread and tyre hardness		65 Shore A
Unit weight	⬆	5.2 kg
Non-marking		✓
Non-staining		✓
Antistatic	☐	×
ESD		×
Electrically conductive	☐	×
Corrosion-resistant		×
Heat-resistant	⬆	×



Tread and tyre hardness

65 Shore A

Rolling resistance


very good

Wear resistance

good

Operating noise / floor surface preservation

very good



Suitable for autoclaves	×
Suitable for machine washing	×