

Data sheet

Hydraulic data

Maximum operating pressure P_N	10 bar
Head max H_{\max}	11.0 m
Flow max Q_{\max}	25.5 m ³ /h
Minimum suction head at 50 °C m	5 m
Minimum suction head at 95 °C m	12 m
Minimum suction head at 110 °C	18 m
Min. fluid temperature T_{\min}	-20 °C
Max. fluid temperature T_{\max}	110 °C
Min. ambient temperature T_{\min}	-20 °C
Max. ambient temperature T_{\max}	40 °C

Motor data

Energy efficiency index (EEI)	0.20
Mains connection	1~230 V ±10%, 50/60 Hz
Min current I_{\min}	0.17 A
Max current I_{\max}	2.65 A
Rated power P_2	500 W
Min. speed n_{\min}	950 1/min
Max. speed n_{\max}	4600 1/min
Power consumption $P_{1\min}$	15 W
Power consumption $P_{1\max}$	600 W
Interference emission	EN 61800-3;2004+A1;2012 /residential area (C1)
Interference immunity	EN 61800-3;2004+A1;2012 /industrial environment (C2)
Threaded cable connection	2 x M20x1.5
Insulation class	F
Protection class	IPX4D

Materials

Pump housing	Cast iron
Impeller	PPS-GF40
Shaft	Stainless steel
Bearing	Carbon, synthetic resin-impregnated

Installation dimensions

Pipe connection on the discharge side DNd	DN 50
Pipe connection on the suction side DNs	DN 50
Port-to-port length Lo	280 mm