



E32-L25L 2M

Fiber optic sensor head, limited reflective, square, top-view, R10 fiber, 2 m cable

Specifications

Sensing method	Limited reflective
Shape	Square
Product Width (unpacked)	18 mm
Product Depth (unpacked)	4 mm
Product Height (unpacked)	16 mm
Application	Object detection
Temperature range	-40-70 °C
Sensing distance	7 mm
Cable length	2 m
Bending radius	10 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP50
Sensing surface orientation	Top-view
Material sheath	Polyethylene

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color
mark sensor



E3NX-CA

High-performance color
mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital
fiber amplifier



E3X-NA

Digital fiber amplifier with
potentiometer adjustment

Downloads

CAD Library



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Sensor Selection Selection Guide

EN PDF 16.2 MB

