

Threaded Rod Cutter LXT®

DSC121

18V • M8 – M12

Powerful, non-sparking and brushless cutter for threaded rods and stainless steel

Powerful, fast and silent threaded rod cutter with a brushless motor. Cuts threaded rods neatly and safely without sparks. The edge created is extremely neat. Can also be used for cutting 8 – 12 mm steel. Up to 500 cuts with a single charge (6.0Ah battery).



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Cutting time	3,0 s
Sound Power Level (L _{WA})	96 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Product Dimensions (L x W x H):	212 x 323 x 260 mm
Tool weight with battery	5,7 - 6,0 kg

User benefits

- Brushless maintenance-free and long-life motor
- No dust, no sparks.
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

821552-6

Makpac case (4)



SC09002700

Cutter Blade Set M8



SC09002710

Cutter Blade Set M10



SC09002720

Cutter Blade Set M12



SC09002730

Cutter W3/8", DSC121



SC09002740

Cutter Blade Set W 1/2"



SC09002750

Cutter Blade Set W 5/16"



Other

User manual

Parts drawing