


FEATURES

- **Material:** Polytetrafluoroethylene: Offers excellent chemical resistance and durability.
- **Maximum Operating Pressure:** 3000 kPa: Ensures reliable sealing under high-pressure conditions.
- **Maximum Operating Temperature:** 280°C: Suitable for high-temperature applications.
- **Rotary Speed:** 18 m/s: Capable of handling high-speed rotary applications.
- **Section:** 5 mm: Provides a compact and efficient sealing solution.

RS PRO 5mm Gland Packing, Polytetrafluoroethylene

RS Stock No: 606-551



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for high-performance sealing applications. Made from durable polytetrafluoroethylene, it is ideal for use in environments requiring high chemical resistance and thermal stability. The packing is suitable for both static and dynamic sealing, providing reliable performance in demanding industrial settings.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------