

KERN SXC 30K-3L

KERN

Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory



Category	
Brand	KERN
Product category	Industrial scale
Product group	Stainless steel platform scale
Product family	SXC
Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	30 kg
Readability [d]	0,002 kg
Reproducibility	0,002 kg
Linearity	± 0,006 kg
Resolution	15.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	30 kg (M1)
Stabilization time	3 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,01 kg
Maximum creep (15 minutes)	8 g
Maximum creep (30 minutes)	16 g
Default unit	kg
Units	kg g lb ffa PCS %
Loadcell type	stainless steel IP68 encapsulated
Load cell connection	6-wire

Display	
Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language
Construction	
Dimension display device (W×D×H)	232×150×77,3 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×120 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Material display housing	stainless steel
Material load cell(s)	Stainless steels
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Transport safety lock - bolt torque	0,1 Nm
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Platform Construction	Single-Cell
Load cells - number	1
Functions	
PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓

KERN SXC 30K-3L

KERN

Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Counting resolution (laboratory conditions)	30.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Hold function	✓
IP protection - complete device	-
IP protection - display	IP68
IP protection - platform	no IP protection
IP protection - load cell	IP68
	5 min
	2 min
	1 min
Auto-off interval(s) in battery mode/rechargeable battery mode	30 min
	60 min
	30 sec
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	7

Interface

Interfaces	RS-232 (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory)
EasyTouch (ET) - Compatibility	vollständig
EasyTouch (ET) - Connection type	KUM

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO

Input voltage power supply / power [Max] 110 V - 240 V AC

Battery / accumulator type Li-Ion

Battery no battery

Rechargeable battery operating time - backlight on 20 h

Rechargeable battery operating time - backlight off 48 h

Rechargeable battery charging time 8 h

Rechargeable battery optional Rchrg. battery optional (factory)

Environmental conditions

Ambient temperature [Min] -10 °C

Ambient temperature [Max] 40 °C

Humity of environment [Min] 0 %

Humity of environment [Max] 80 %

Approval

CE mark ✓

Services (optional)

Article number for adjustment at the location of installation 961-248

Article number for DAkkS calibration 963-128

Article number for certificate of conformity (verification) 969-517

Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 490×790×235 mm

Net weight 20,8 kg

Shipping method Parcel service

Net weight approx. 22 kg

Gross weight approx. 24 kg

Shipping weight 23,7 kg


KERN SXC 30K-3L

KERN

Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Pictograms

STANDARD



OPTION



FACTORY

