



EXPERIENCE TO PERFORM

## TECHNICAL DATA SHEET

# DIESEL ANTI-FREEZE

### - **PRODUCT DESCRIPTION**

**DIESEL ANTI-FREEZE** is an additive developed to improve diesel fuel fluidity at low temperatures and to prevent setting of wax crystals. Prevents the crystallization of paraffin clogging the filter. Protects from the crystallisation of paraffin at temperature as low as -20°C depending on the type of diesel fuel. Eliminates the effects of possible contamination of the fuel with water.

- Prevents the crystallization of paraffin clogging the filter.
- Prevents deposits and rust formation.
- Reduced smoke emission
- Eliminates the effects of possible contamination of the fuel with water

### - **FIELDS OF USE**

Additive for all diesel engines in cold season.

### - **TECHNICAL SPECIFICATIONS**

Appearance	Liquid
Color	Straw-yellow
Smell	Typical
Density at 15°C ASTM D1298	0,840 g/ml
Viscosity at 40°C	3 mm <sup>2</sup> /s
Flash Point	> 61°C

The reported data are subject to normal manufacturing tolerances

### - **METHOD OF USE**

For best results, use one bottle in a tank (40 ÷ 50 litres of diesel fuel).

### - **DOSAGE**

The content of a 250 ml package is enough for the treatment of 50 liters of diesel fuel.

**DIESEL ANTI-FREEZE** guarantees fuel pumpability at temperature as low as -20°C depending on the type of diesel fuel.

### - **STORAGE**

Unopened and stored at room temperature away from direct sunlight, for at least 3 years.

### - **PACKAGING**

PVC bottle

Contents 250 ml

Product code: 9650

Languages on label: IT/EN/FR/DE/NL

Product code: 31037

Languages on label: IT/EN/FR/DE/NL

Product code: 34037

Languages on label: EN/EL/ES/PT/PL

### - **NOTES**

For information on product safety, please consult Material Safety Data Sheets.

TS 23-10-2024

The data contained herein are the result of technological research by our laboratories and are given for informative purposes only. We exclude any liability deriving from the incorrect choice or application of the product and from the lack of the necessary precautions, which should be carefully checked by the user. For information, please contact our Technical Dept. on no. +39 02924361

**AREXONS S.p.A.** A SOCIO UNICO  
Via Antica di Cassano, 23  
20063 Cernusco sul Naviglio (MI) Italy  
Capitale Sociale: € 15.000.000,00 I.V.  
Registro delle Imprese di Milano n. 09728360968  
Codice Fiscale e Partita IVA 09728360968  
Direzione e coordinamento ex art. 2497 c.c. PLI (Netherlands) B.V.  
Centralino 02 92436.1  
Fax 02 92436.306  
[www.arexons.com](http://www.arexons.com)

A wholly-owned subsidiary of **PETRONAS**

Sistemi di gestione di qualità della società Arexons S.p.A.  
certificati ISO 9001 da LRQA.

Sistemi di gestione di ambiente e sicurezza della società Arexons S.p.A.  
certificati ISO 14001 e OHSAS 18001 da Bureau Veritas.

