

Vacuum Cleaner LXT®

DCL184

18V • 54 mbar • 0.5 l

Excellent vacuum cleaner for cleaning car interiors and other compact areas

Battery-powered vacuum cleaner specially designed for cleaning car interiors. Four different types of nozzles ideal for vacuuming a car. Convenient blowing function to, for example, dry the car prior to waxing. Operating time 20 minutes with 18V LXT® 3.0Ah battery.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Air volume	1,4 m³/min
Max. sealed suction	54 mbar
Vacuum hose length	1,0 m
Dust Bag Capacity	0,5 L
Sound Pressure Level (L _{pA})	58 / 65 / 68 dB(A)
Vibration Level (3 axes)	≤ 0,4 m/s²
Tool weight with battery	1,8 - 2,2 kg
Product Dimensions (L x W x H):	365 x 138 x 202 mm
Continuous Use 18V / 3.0 Ah Battery	80 / 30 / 20 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Suction power	5 / 23 / 38 W
Product net weight	1,5 kg

User benefits

- Low noise level for pleasant work.
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Variable suction power control by dial

Link to product - www.makitauk.com



Related products

Optional AC

140H94-2

Soft Brush 360 Complete Set, Blue



140H95-0

Seat Nozzle, Ø32 Mm



162544-9

Shoulder Belt, CL121D



191D67-4

Round brush



191M30-1

Brush Nozzle



199041-2

Seat nozzle set



Other

User manual

Parts drawing