


Data Sheet | Item Number: 2587-2147

Switched-mode power supply; Base; 1-phase; 24 VDC output voltage; 20 A output current; DC-OK LED

<https://www.wago.com/2587-2147>



Similar to illustration

Features:

- Optical status indication
- Suitable for both parallel and series operation
- Natural convection cooling when horizontally mounted
- Connection technology with push-in termination
- Electrically isolated output voltage (SELV) per EN 62368-1/UL 61010-1



Technical data

Input		Output	
Phases	1	Nominal output voltage $U_{o\,nom}$	24 VDC (SELV)
Nominal input voltage $U_{i\,nom}$	1 x 100 ... 240 VAC	Output voltage range	23.5 ... 28 VDC (adjustable)
Input voltage range	1 x 90 ... 264 VAC (Derating -1 %/V for voltage < 100 VAC)	Default Setting	DC 24 V
Nominal mains frequency range	50 Hz / 60 Hz	Nominal output current $I_{o\,nom}$	20 A
Input current I_i	≤ 7 A	Nominal output power	480 W
Inrush current	≤ 20 A (at 230 VAC / 25 °C)	Deviation	≤ 1 %
Power factor	≥ 0.98 (230 VAC)	Residual ripple	≤ 100 mV (peak-to-peak)
Power factor correction (PFC)	Active	Overload behavior	Shutdown and automatic restart in the event of a short circuit
Mains failure hold-up time	≥ 16 ms (230 VAC)		

Signaling and communication	
Signaling	Optical status indication (DC OK)

Efficiency/power losses	
Power loss P_i	≤ 5 W (no load); ≤ 32.5 W (Full load)
Efficiency (typ.)	94 %

Circuit protection	
Internal fuse	T 8 A / 250 V

Safety and protection	
Isolation voltage (pri.-sec., AC)	3510 V
Isolation voltage (pri.-PE, AC)	2210 V
Protection class	I
Protection type	IP20; per EN 60529
Overvoltage category	III (≤ 2000 m); II (> 2000 m)
Pollution degree	2
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes
MTBF	> 1,000,000 h (at 25 °C; per IEC 61709; SN 29500)

Connection data

Connection 1	
Connection type 1	Input/output
Connection technology	Push-in CAGE CLAMP®
WAGO connector	WAGO Serie 2626
Solid conductor	0.2 ... 10 mm² / 24 ... 8 AWG
Fine-stranded conductor	0.2 ... 10 mm² / 24 ... 8 AWG
Fine-stranded conductor; with insulated ferrule	0.25 ... 6 mm²
Fine-stranded conductor; with uninsulated ferrule	0.25 ... 6 mm²
Strip length	13 ... 15 mm / 0.51 ... 0.59 inches



Physical data		
Width		56 mm / 2.2 inches
Height		125 mm / 4.92 inches
Depth from upper-edge of DIN-rail		138 mm / 5.43 inches

Mechanical data		
Mounting type		DIN-35 rail

Material data		
Fire load		0 MJ
Weight		1149 g

Environmental requirements		
Ambient temperature (operation)		-30 ... +70 °C (device starts at -40 °C (type-tested))
Ambient temperature (storage)		-40 ... +85 °C
Relative humidity		5 ... 96 % (no condensation permissible)
Derating		-9.6 W/°C (> 45 °C and < 200 V); -9.6 W/°C (> 50 °C and ≥ 200 V)
Climatic category		3K3 (per EN 60721)
Operating altitude (max.)		5000 m

Standards and specifications		
Conformity marking		CE
Standards/specifications		EN 62368-1 EN 55032 EN 55035 EN IEC 61000-3-2 EN 61000-3-3 EN IEC 61000-6-4 EN IEC 61000-6-2 UL 61010-1 UL 61010-2-201

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		CN
GTIN		4066966626698
Customs tariff number		85044083900

Product classification		
UNSPSC		39121004
ETIM 9.0		EC002540
ETIM 8.0		EC002540
ECCN		NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates

General approvals			Declarations of conformity and manufacturer's declarations		
					
Approval	Standard	Certificate Name	Approval	Standard	Certificate Name
UL	UL 61010-2-201	E255817	EU-Declaration of Confor- mity	-	-
Underwriters Laboratories Inc.			WAGO GmbH & Co. KG		
			UK-Declaration of Confor- mity	-	-
			WAGO GmbH & Co. KG		

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 2587-2147	

Documentation

Bid Text				Instruction Leaflet			
2587-2147	14.04.2025	docx	45.37 KB		Power Supply BASE	V 3.0.0	pdf
						10.09.2024	653.79 KB
2587-2147	14.04.2025	x81	7.24 KB				

CAD/CAE-Data

CAD data	
2D/3D Models	
2587-2147	