

mini slide DGST-12-40-PA

Part number: 8085126

FESTO



Data sheet

Feature	Value
Stroke	40 mm
Adjustable endposition range/front length	21.1 mm
Adjustable endposition range/rear length	21.5 mm
Piston diameter	12 mm
Operating mode of drive unit	Yoke
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Guide	Recirculating ball bearing guide
Design structure	twin piston Yoke Piston rod Slide
Position detection	For proximity sensor
Operating pressure	1 ... 8 bar
Max. speed	0.8 m/s
Repetition accuracy	≤ 0,3 mm
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 60 °C
Impact energy in end positions	0.12 Nm
Cushioning length	1.3 mm
Max. force F _y	560 N
Max. force F _z	560 N
Max. torque M _x	5.8 Nm
Max. torque M _y	5.8 Nm
Max. torque M _z	5.8 Nm
Theoretical force at 6 bar, return stroke	102 N
Theoretical force at 6 bar, advance stroke	136 N
Moving mass	307 g
Product weight	609 g
Mounting type	with through hole
Pneumatic connection	M5
Materials note	Free of copper and PTFE Conforms to RoHS
Material cover	Wrought Aluminium alloy
Material seals	HNBR
Material of guide	POM TPE-E High alloy steel
Material housing	Wrought Aluminium alloy
Material piston rod	High alloy steel, non-corrosive