


Product datasheet

Specifications



"PanelSet SFM mounting plate - 1000x800 mm - 20M"

NSYMP20M8

EAN Code: 3606480850622

Main

Range	PanelSeT
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Compartmentalised application
Enclosure nominal dimensions	- W: 800 mm
Number of modules	20
Mounting plate description	Plain
Range compatibility	PanelSeT SFM
Device composition	1 mounting plate
Quantity per set	Set of 1
Material	Galvanised steel

Complementary

Fixing mode	By fixing brackets
Adjustment	Adjustable in depth every 50 mm
Height	Nominal: 1000 mm
Width	Nominal: 800 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	96.000 cm
Package 1 Width	69.500 cm
Package 1 Length	1.500 cm
Package 1 Weight	11.380 kg
Unit Type of Package 2	P12
Number of Units in Package 2	25
Package 2 Height	35.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	304.000 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty (in months) 18



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	117 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	61 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	23 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.4 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	32 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	98
End of life manual availability	No need of specific recycling operations
Take-back	No