

För icke direkt toleranssatta mått gäller toleransklass
 General tolerances if not otherwise stated

--

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2


Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
 No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.
 Additional general tolerances in accordance with drawing 4100-4644.

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
 This drawing is the property of Pressmaster AB. Protected in accordance with prevailing law.

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
1	1021471000	A 4300-3149/AAB	041129	TGW
2	1021525000	4101-3036 W 4101-2956	041202	TGW



Packas enligt förpackningsritning 4101-3584
 Packed according to drawing 4101-3584

4101-3495
 A
 B

1	4300-3149/AAB	4101-3765 POSITION A	4101-3583	4101-3585	4101-3036	2 2
	4300-3149/AAA	4101-3582 POSITION A	4101-3583	4101-3585	4101-3036	
	ART.NR.VAR.	A	B	C	D	

Material		Behandling/Treatment			Status	
Konstr./Design		Ritad/Drawn	Datum/Date	Skala/Scale	Kontr./Checked	Godk./Approved
TGW		TGW	2004-12-02	1:1	SE	NE
pressmaster <small>REG NR FM3607</small>				Benämning/Denomination MOBILE TOOL MOBILE TOOL		Vikt/Weight,gram 43003149
					Art grp	REV
					012	002