

CARBIDE TIPPED

TUNGSTEN CARBIDE TIPPED MULTI PURPOSE

MPH Hole Saws will power through wood, MDF, plastics, plasterboard and ceramic wall tiles. Cutting speeds will be up to five times faster than a bi metal hole saw cutting the same material. For installers, our range of kits provide the perfect solution to all your cutting needs.

FEATURES

- Rapid, heat free stock removal of wood, MDF, plastics, plasterboard, and ceramic tiles.
- Carbide tipped teeth for outstanding cutting performance and product durability.
- Smooth cutting with minimal heat build up.
- Suitable for use in electric and battery powered tools.
- Hole saw depth of 54mm (2.1/8").
- Special arbors featuring extended length pilot drills are available, alternatively fit the longer A014CE pilot drill to our standard Starrett arbors.





	Diameter	
Cat. No.	mm	Inch
MPH0034	19mm	3/4″
MPH2532	20mm	25/32"
MPH0078	22mm	7/8″
MPH0100	25mm	1″
MPH0116	27mm	1.1/16″
MPH0118	29mm	1.1/8″
MPH0136	30mm	1.3/16″
MPH0114	32mm	1.1/4″
MPH0138	35mm	1.3/8″
MPH0112	38mm	1.1/2″
MPH0196	40mm	1.9/16″
MPH0158	41mm	1.5/8″
MPH0134	44mm	1.3/4″
MPH0178	48mm	1.7/8″
MPH0200	51mm	2″

Cat. No.	mm	Inch
MPH0218	54mm	2.1/8″
MPH0214	57mm	2.1/4″
MPH0238	60mm	2.3/8″
MPH0212	64mm	2.1/2″
MPH0296	65mm	2.9/16″
MPH0258	67mm	2.5/8″
MPH0234	70mm	2.3/4″
MPH0278	73mm	2.7/8″
MPH0300	76mm	3″
MPH0318	79mm	3.1/8″
MPH0314	83mm	3.1/4″
MPH0338	86mm	3.3/8″
MPH0312	89mm	3.1/2″
MPH0358	92mm	3.5/8″

Diameter

	Diameter	
Cat. No.	mm	Inch
MPH0334	95mm	3.3/4″
MPH0378	98mm	3.7/8″
MPH0400	102mm	4″
MPH0418	105mm	4.1/8″
MPH0414	108mm	4.1/4″
MPH0456	109mm	4.5/16"
MPH0438	111mm	4.3/8″
MPH0412	114mm	4.1/2″
MPH0458	118mm	4.5/8″
MPH0434	121mm	4.3/4″
MPH0500	127mm	5″
MPH0512	140mm	5.1/2″
MPH0600	152mm	6″
MPH0614	159mm	6.1/4″



